


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #11-682 3-4 DAYS

[Other Coating Options](#)



1



€132,00

ADD TO CART

Qty 1-5

€132,00

Qty 6+

€116,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):  
350.41 @587.6nm

Back Focal Length BFL (mm):

|                                                                                               |
|-----------------------------------------------------------------------------------------------|
| 349.31                                                                                        |
| <b>Coating:</b><br>BBAR (370-550nm)                                                           |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <0.55% @ 370 - 550nm                        |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980)     |
| <b>Surface Quality:</b><br>20-10                                                              |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                         |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/8                                                   |
| <b>Focal Length Tolerance (%):</b><br>±1                                                      |
| <b>Centering (arcmin):</b><br><3                                                              |
| <b>Center Thickness CT (mm):</b><br>1.60 ±0.10                                                |
| <b>Edge Thickness ET (mm):</b><br>1.1                                                         |
| <b>Radius R<sub>1</sub> (mm):</b><br>160.65                                                   |
| <b>Clear Aperture CA (mm):</b><br>22.86                                                       |
| <b>f/#:</b><br>13.78                                                                          |
| <b>Numerical Aperture NA:</b><br>0.037                                                        |
| <b>Type:</b><br>Plano-Convex Lens                                                             |
| <b>Bevel:</b><br>Protective bevel as needed                                                   |
| <b>Wavelength Range (nm):</b><br>370 - 550                                                    |
| <b>Angle of Incidence (°):</b><br>0                                                           |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>7.5 J/cm² @ 355nm, 20ns, 20Hz |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |