

25.4mm Dia f/4 VIS Coated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock **#48-184** 3-4 DAYS

⊖ 1 ⊕

€65,00

ADD TO CART

Qty 1-10

€65,00

Qty 11+

€53,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40 ±0.1

Effective Focal Length EFL (mm):
102.00 @632.8nm

Numerical Aperture NA: 0.12
Back Focal Length BFL (mm): 98.00
Substrate: ☐ PMMA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 632.8
Coating: BBAR (450-650nm)
Coating Specification: R _{avg} <0.5% @ 450 - 650nm
Clear Aperture CA (mm): 23.9
Edge Thickness ET (mm): 4.00
Center Thickness CT (mm): 5.45
f/#: 4.00
Bevel: Protective bevel as needed
Operating Temperature (°C): 80.00
Radius R (mm): 49.78
Type: Aspheric Lens
Wavelength Range (nm): 450 - 650
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View