

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



25mm Focal Length



Stock **#63-782** ☐ In Stock



1



€850,00

ADD TO CART

Qty 1+

€850,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:  
Variable

Length (mm):  
41.07

Horizontal Field of View, 1/2" Sensor:  
56.6mm - 14.7°

Horizontal Field of View, 2/3" Sensor:

|                                                                                                                                |
|--------------------------------------------------------------------------------------------------------------------------------|
| 78mm - 20.2°                                                                                                                   |
| <b>Filter Thread:</b><br>M25.5 x0.50 (Female)                                                                                  |
| <b>Maximum Diameter (mm):</b><br>37.5                                                                                          |
| <b>Weight (g):</b><br>96                                                                                                       |
| <b>Horizontal Field of View, 1/3" Sensor:</b><br>42.4mm - 11.1°                                                                |
| <b>Maximum Rear Protrusion (mm):</b><br>2.81                                                                                   |
| <b>Maximum Image Circle (mm):</b><br>11.00                                                                                     |
| <b>Numerical Aperture NA, Object Side:</b><br>0.0298                                                                           |
| <b>Horizontal Field of View @ Max Sensor Format:</b><br>78mm - 20.2°                                                           |
| <b>Number of Elements (Groups):</b><br>9 (6)                                                                                   |
| <b>Horizontal Field of View, 1/1.8" Sensor:</b><br>63.8mm - 16.6°                                                              |
| <b>Horizontal Field of View, 1/2.5" Sensor:</b><br>51.3mm - 13.4°                                                              |
| <b>Type:</b><br>Fixed Focal Length Lens                                                                                        |
| <b>Focal Length FL (mm):</b><br>25.00                                                                                          |
| <b>Primary Magnification PMAG:</b><br>0.113                                                                                    |
| <b>Maximum Sensor Format:</b><br>2/3"                                                                                          |
| <b>Working Distance (mm):</b><br>200 - ∞                                                                                       |
| <b>Mount:</b><br>C-Mount                                                                                                       |
| <b>Aperture (f/#):</b><br>f/1.8 - f/22                                                                                         |
| <b>Coating:</b><br>425 - 675nm BBAR                                                                                            |
| <b>Coating Specification:</b><br>425 - 675nm BBAR                                                                              |
| <b>Entrance Pupil Position (mm):</b><br>17.67                                                                                  |
| <b>Horizontal Field of View, 1/4" Sensor:</b><br>31.8mm - 8.3°                                                                 |
| <b>Object Space Principal Plane (mm):</b><br>30.53                                                                             |
| <b>Image Space Principal Plane (mm):</b><br>-11.19                                                                             |
| <b>Field of View at Max Sensor Format:</b><br>Horizontal: 78mm - 20.2°<br>Vertical: 58.4mm - 15.2°<br>Diagonal: 97.8mm - 25.1° |
| <b>Maximum Distortion (%):</b><br>0.1                                                                                          |
| <b>Exit Pupil Position (mm):</b><br>-38.04                                                                                     |
| <b>Optimized Working Distance (mm):</b><br>1500 - ∞                                                                            |
| <b>Lens Wavelength Range:</b><br>VIS                                                                                           |
| <b>Imaging Lens Type:</b><br>High Performance Lens                                                                             |
| <b>Storage Temperature (°C):</b><br>-20 to +60 For questions regarding operating temperature please contact our support team   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

