

## TECHSPEC® 25mm 532nm, Laser Line Non-Polarizing Cube Beamsplitter



Laser Line Non-Polarizing Cube Beamsplitters



Stock #35-960  In Stock

1 **€276,00**

**ADD TO CART**

Qty 1-5

€276,00

Qty 6+

€221,00

Volume Pricing

[Request Quote](#)

**!** Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Beam Deviation (arcmin):**  
±2

**Bevel:**  
Protective as needed

**Clear Aperture (%):**  
90

**Coating Specification:**  
<0.25% Reflection on Entrance and Exit Faces

**Construction:**  
Cube

**Design Wavelength DWL (nm):**  
532

**Dimensions (mm):**  
25.0 x 25.0 x 25.0 ±0.1

**Reflection/Transmission Tolerance (%):**  
±5

**Substrate:**   
[N-BK7](#)

**Surface Quality:**  
40-20

**Transmission (%):**  
<45% ±5% @ DWL

**Type:**  
Non-Polarizing Beamsplitter

**|Ts-Tp|:**  
<3% @ DWL

**Power (fringes) @ 632.8nm:**  
1.50

**Irregularity (fringes) @ 632.8nm:**  
0.25

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Reach 219:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

---