

TECHSPEC<sup>®</sup> 25.4mm Dia. x 250mm FL, 8-12μm BBAR Coated, ZnSe Plano-Convex Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock **#39-553** **2 In Stock**

[Other Coating Options](#)

-

1

+

€515<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | €515,00 each                  |
| Qty 11-25      | €463,50 each                  |
| Qty 26-49      | €286,34 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

|                                   |                                                  |
|-----------------------------------|--------------------------------------------------|
| Plano-Convex Lens                 | Type:                                            |
| Physical & Mechanical Properties  |                                                  |
| 25.40 +0.00/-0.10                 | Diameter (mm):                                   |
| ≤12.7                             | Centering, ETD (μm):                             |
| 2.40 ±0.10                        | Center Thickness CT (mm):                        |
| 2.17                              | Edge Thickness ET (mm):                          |
| 22.86                             | Clear Aperture CA (mm):                          |
| Protective as needed              | Bevel:                                           |
| <50 RMS                           | Surface Roughness (□):                           |
| Optical Properties                |                                                  |
| 250.00 @ 10.6μm                   | Effective Focal Length EFL (mm):                 |
| 249                               | Back Focal Length BFL (mm):                      |
| BBAR (8000-12000nm)               | Coating:                                         |
| R <sub>avg</sub> ≤0.5% @ 8 - 12μm | Coating Specification:                           |
| Coherent® Infrared ZnSe           | Substrate: □                                     |
| 40-20                             | Surface Quality:                                 |
| λ                                 | Power (P-V) @ 632.8nm:                           |
| N20                               | Irregularity (P-V) @ 10.6μm:                     |
| 350.67                            | Radius R <sub>1</sub> (mm):                      |
| 9.84                              | f/#:                                             |
| 0.05                              | Numerical Aperture NA:                           |
| 8000 - 12000                      | Wavelength Range (nm):                           |
| <0.0005 @ 10.6μm                  | Bulk Absorption Coefficient (cm <sup>-1</sup> ): |
| Electrical                        |                                                  |
| N10                               | Power (P-V) @ 10.6μm:                            |
| Regulatory Compliance             |                                                  |
| Compliant                         | RoHS 2015:                                       |
| View                              | Certificate of Conformance:                      |
| Compliant                         | Reach 242:                                       |

## PRODUCT DETAILS

- Edmund Optics® Designed, Coherent® Manufactured
- Premier Grade ZnSe Material
- Uncoated or Broadband AR Coating Options


TECHSPEC® Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses are designed for focusing or collimation applications in the mid-wave and longwave infrared spectrum. Manufactured by Coherent®, these lenses feature Infrared ZnSe material with <0.0005cm<sup>-1</sup> bulk absorption at 10.6μm and are available uncoated or with a variety of broadband anti-reflection coating options. The 8-12μm coating is ideal for use with CO<sub>2</sub> lasers and thermal camera applications, whereas the dual band 3-12μm coating is ideal for hyperspectral applications. TECHSPEC® Zinc Selenide PCX Lenses feature an irregularity of <N20 at 10.6μm, 40-20 surface quality, and <50Å surface roughness. Three diameter options are available, with effective focal lengths ranging from 12.7mm to 250mm.

**Notes:** II-VI Incorporated is now Coherent Corp.

Special care should be taken when handling Zinc Selenide as it is a toxic material. Always wear rubber or plastic gloves to avoid risk of contamination.


## TECHNICAL INFORMATION

Uncoated – 6.3mm Thickness



AR COATED ZINC SELENIDE

ZnSe with 3-12μm AR Coating  
Typical Transmission



Typical transmission of a ZnSe window with BBAR (3000-12000nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} < 5.0\% @ 3 - 12\mu m$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

ZnSe with 8-12μm AR Coating  
Typical Transmission



Typical transmission of a ZnSe window with BBAR (8000-12000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% @ 8 - 12\mu m$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

SPECIAL HANDLING

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## COMPATIBLE MOUNTS

---