

TECHSPEC®

25.4mm Dia. x 25.4mm EFL, Protected Aluminum 90° OAP Mirror with Alignment Through Holes



#11-770

Stock **#11-770** 5 In Stock

-

1

+

€267⁸⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€267,80 each
Qty 6-25	€241,02 each
Qty 26-50	€227,63 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Off-Axis Parabolic Mirror		Type:
Physical & Mechanical Properties		
25.40 +0.00/-0.10	Diameter (mm):	
<50 RMS	Surface Roughness (Ra):	
25.40	Y Offset (mm):	
Through Hole Orientation:		
1 x Parallel to Focused Beam		
1 x Parallel to Collimated Beam		
4.1	Through Hole Diameter (mm):	
Optical Properties		
25.40	Effective Focal Length EFL (mm):	
±1	Focal Length Tolerance (%):	
25.40	Radius of Curvature (mm):	
Protected Aluminum (400-2000nm)	Coating:	
Metal	Coating Type:	
Coating Specification:		
Ravg >85% @ 400 - 700nm		
Ravg >90% @ 400 - 2000nm		
90	Off-Set Angle (°):	
12.7	Parent Focal Length PFL (mm):	
λ/8	Surface Figure, RMS:	
400 - 2000	Wavelength Range (nm):	
80-50	Surface Quality:	
Aluminum 6061-T6	Substrate:	
Regulatory Compliance		
View	Certificate of Conformance:	



PRODUCT DETAILS

- Through Holes Parallel to Focused and Collimated Beams
- Range of Metallic Coatings Available
- <50Å RMS Surface Roughness

TECHSPEC® Off-Axis Parabolic (OAP) Mirrors with Alignment Through Holes are designed with two through holes, one that aligns with the focal point of beams focused off the parabolic surface and the second parallel to beams collimated by the surface. The hole placements allow for two beams to hit a target or sample simultaneously, which is a technique used to take pump-probe measurements. These OAPs feature aluminum substrates and are diamond turned with a surface roughness of <50Å RMS that minimizes scatter. TECHSPEC Off-Axis Parabolic Mirrors with Alignment Through Holes are available coated with protected gold, protected aluminum, or UV enhanced aluminum for integration into applications requiring high reflectance from the ultraviolet (UV) to the infrared (IR).

Note: Please [contact us](#) for custom options if your application requires a [standard OAP Mirror](#) with a through hole.

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).