

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.4mm Dia. X 38.1mm FL, VIS-NIR, Inked, Achromatic Lens



Stock #49-791-INK [CONTACT US](#)

[Other Coating Options](#)



1



€128,00

ADD TO CART

Qty 1-5

€128,00

Qty 6+

€102,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 ±0.025

Effective Focal Length EFL (mm):

38.10
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 30.77
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 24.40
Centering (arcmin): <1
Center Thickness CT (mm): 13.50 ±0.20
Center Thickness CT 1 (mm): 10.50 ±0.10
Center Thickness CT 2 (mm): 3.00 ±0.10
Radius R ₁ (mm): 26.37
Radius R ₂ (mm): -20.43
Radius R ₃ (mm): -101.75
Edge Thickness ET (mm): 9.44
Substrate:  N-BAF10 / N-SF6
Surface Quality: 40-20
f/#: 1.5
Numerical Aperture NA: 0.33
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View