

25.4mm Dia. x 50.8mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF₂) DCX Lens | CF-BX-25-50

See More by [ISP Optics](#)



Calcium Fluoride Double-Convex (DCX) Lenses

Stock **#47-057** 3-4 DAYS



1



€263,00

ADD TO CART

Qty 1+

€263,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.13

Effective Focal Length EFL (mm):
50.80

Coating:
Uncoated

Substrate: Calcium Fluoride (CaF₂)
Surface Quality: 60-40
Clear Aperture (%): 90.00
Centering (arcmin): <3
Bevel: Protective bevel as needed
Center Thickness CT (mm): 6.20
Center Thickness Tolerance (mm): ±0.2
Edge Thickness ET (mm): 2.00
Radius R₁=R₂ (mm): 39.61
Back Focal Length BFL (mm) @ DWL: 48.51
Effective Focal Length EFL @ 0.6328μm (mm): 46.86
Effective Focal Length EFL @ 1.064μm (mm): 47.33
Effective Focal Length EFL @ 2.94μm (mm): 48.47
Effective Focal Length EFL @ 5.0μm (mm): 50.80
f/#: 2.00
Focal Length Specification Wavelength (μm): 5.00
Focal Length Tolerance (%): ±2 @DWL
Numerical Aperture NA: 0.25
Surface Accuracy: 1λ
Type: Double-Convex Lens
Wavelength Range (μm): 0.35 - 7
Wavelength Range (nm): 350 - 7000
Model Number: CF-BX-25-50

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View