

25mm Dia. BaF₂, IR Holographic Wire Grid Polarizer



25mm Dia. BaF₂, IR Holographic Wire Grid Polarizer, #62-770

Stock **#62-770** ☐ In Stock

-

1

+

€1.520,00

ADD TO CART

Qty 1-5
€1.520,00
Qty 6+
€1.215,00
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads	
Angle of Incidence (°): 0	
Clear Aperture CA (mm): 18.0	
Diameter (mm):	

25.00
Extinction Ratio: 150:1 @ 3μm, 300:1 @ 10μm
Substrate: ☐ Barium Fluoride (BaF ₂)
Operating Temperature (°C): -20 to 75
Polarization: Notches on polarizer ring are aligned with wires of wire grid
Thickness (mm): 2.00
Transmission (%): >65
Type: Linear Polarizer
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Construction: Wire Grid
Groove Parallelism to Edge (°): N/A
Mount Thickness (mm): 5.0
Note: Notches on polarizer ring are aligned with wires of wire grid (max. reflection)
Ring Thickness (mm): ±0.1
Wavelength Range (nm): 2500 - 12000
Surface Flatness (P-V): λ/20 @ 10.6μm
Damage Threshold, By Design: ☐ 50 W/cm ²
Mount: Black Anodized Aluminum
Groove Density (grooves/mm): 2700.00
Mount Thickness Tolerance (mm): +0.2/-0.1

Regulatory Compliance

RoHS: Compliant
Reach 219: Compliant
Certificate of Conformance: View