



25mm Dia. Hexa-Black™ Panel

See More by [Acktar](#)



Acktar Hexa-Black™ Panel



Stock **#37-830** **5 In Stock**

-

1

+

€181^{,65}

ADD TO CART

Volume Pricing	
Qty 1+	€181,65 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

HBP-25-3

Model Number:

Note:

Ships with a low outgassing adhesive sticker that can be applied to the back surface

Physical & Mechanical Properties

	Diameter (mm):
25.00	
	Construction:
Hexa-Black™ Panel	

	Adhesive Thickness (µm):
60	
	Thickness (mm):
3.00	

Optical Properties

	Coating:
Vacuum Black™	
	Wavelength Range (µm):
0.3 - 5	

	Absorbance (AOI > 60) (%):
99.995	

Material Properties

	Absorbance (%):
99.9	

Environmental & Durability Factors

	Operating Temperature (°C):
-50 to 150	
	Abrasion Resistance:
High	

	Humidity Resistance:
ML-C-48497A	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	

	Reach 247:
Compliant	


PRODUCT DETAILS

- Mountable Acktar Spectral Black™, Metal Velvet™, and Hexa-Black™ Technologies
- High Performance from UV to MMIR and UV to LWIR
- Low Hemispherical Reflectance

Acktar Light Absorbent Panels are the optimum solution for absorbent black out materials. Light Absorbing Panels are easily integrated into an optical system using either an optical mount compatible with 25mm optics or the included adhesive sticker. With specular absorbance up to 99.9%, Spectral Black™ and Metal Velvet™ panels offer superior light absorption performance. The Hexa-Black™ versions feature wide-band absorption at grazing angles out to 88°. Acktar Light Absorbent Panels are typically used as black out materials and are ideal for Raman Spectroscopy, Endoscopy, Laser Beam Dumps, and many other applications.

Note: Larger sizes and custom options are available upon request by [contacting technical support](#). All panels have no adhesive pre-applied to the back surface. Each panel ships with an optional adhesive sticker that can be applied to the back surface of the panel.

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
