


25mm Dia. HC VIS-NIR Polarizer, Mounted



Stock **#90-389** NEW **2 In Stock**

-

1

+

€975^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	€975,00 each
Qty 11+	€925,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer

Type:

Physical & Mechanical Properties

23.75

Clear Aperture CA (mm):

25.00

Diameter (mm):

Nanoparticle	Construction:
95	Clear Aperture (%):
Optical Properties	
Double-Side AR Coat	Coating:
>100,000:1 (700nm) >10,000:1 (600 to 850nm) >1,000:1 (600 to 1000nm)	Extinction Ratio:
Sodium Silicate Glass Doped with Glass Nanoparticles	Substrate: ☐
40-20	Surface Quality:
>78%	Transmission (%):
<λ/4 @ 633nm per 1cm	Transmitted Wavefront, P-V:
<1	Beam Deviation (arcmin):
<0.5 (to indicated edge)	Polarization Axis Mark (%):
600 - 1000	Wavelength Range (nm):
Continuous block Continuous pass Pulse peak power Equivalent pulse power density 10 W/cm² 25 W/cm² 12 MW/cm² 1 μJ/cm²	Damage Threshold, By Design: ☐
±20	Acceptance Angle (°):
Threading & Mounting	
Anodized Aluminuim Mbunt	Mount Thickness (mm):
5.00	Mount:
Environmental & Durability Factors	
-20 to +120	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Multiple Wavelength Ranges for UV, VIS and NIR
- >100,000:1 Contrast Ratios Available
- Ideal for Use in Harsh Environments

UV, VIS-NIR, and NIR High Contrast Polarizers offer both versatility and performance over a wide range of wavelengths. These polarizers contain uniformly stretched silver nano-particles in a 220 ±25µm thick soda-lime glass laminated on a thicker soda-lime substrate for increased durability. UV, VIS-NIR, and NIR High Contrast Polarizers are ideal for harsh environments, can withstand up to 120°C, are resistant to UV-radiation and chemicals, and can be safely used in humid environments.

Technical Information

