

**TECHSPEC® 25mm Dia. x 100mm FL UV-VIS Coated, UV Plano-Convex Lens**



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#48-825** 3-4 DAYS

⊖ 1 ⊕

**€155,00**

ADD TO CART

Qty 1-5

€155,00

Qty 6+

€124,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
25.00 +0.0/-0.025

**Effective Focal Length EFL (mm):**

|                                                                                                                                        |
|----------------------------------------------------------------------------------------------------------------------------------------|
| 100.00 @587.6nm                                                                                                                        |
| <b>Back Focal Length BFL (mm):</b><br>97.40                                                                                            |
| <b>Coating:</b><br>UV-VIS (250-700nm)                                                                                                  |
| <b>Coating Specification:</b><br>R <sub>abs</sub> ≤1.0% @ 350 - 450nm<br>R <sub>avg</sub> ≤1.5% @ 250 - 700nm                          |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980)                                              |
| <b>Surface Quality:</b><br>40-20                                                                                                       |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                                                                  |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                                                            |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                                               |
| <b>Centering (arcmin):</b><br><1                                                                                                       |
| <b>Center Thickness CT (mm):</b><br>3.79 ±0.10                                                                                         |
| <b>Edge Thickness ET (mm):</b><br>2.05                                                                                                 |
| <b>Radius R<sub>1</sub> (mm):</b><br>45.85                                                                                             |
| <b>Clear Aperture CA (mm):</b><br>24                                                                                                   |
| <b>f/#:</b><br>4                                                                                                                       |
| <b>Numerical Aperture NA:</b><br>0.13                                                                                                  |
| <b>Type:</b><br>Plano-Convex Lens                                                                                                      |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                            |
| <b>Wavelength Range (nm):</b><br>250 - 700                                                                                             |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>3 J/cm <sup>2</sup> @ 355nm, 10ns<br>5 J/cm <sup>2</sup> @ 532nm, 10ns |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |