

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25mm Dia., 0.85 Numerical Aperture NIR Coated, Aspneric Lens



Stock #67-259 3-4 DAYS

[Other Coating Options](#)



1



€430,00

ADD TO CART

Qty 1-5

€430,00

Qty 6+

€344,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
15.00 @ 587.6nm

Numerical Aperture NA:

0.83
Back Focal Length BFL (mm): 8.42
Substrate: ☐ N-SF5
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (600-1050nm)
Coating Specification: R _{avg} ≤1.5% @ 600 - 1050nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 1.64
Center Thickness CT (mm): 11.00 ±0.1
f/#: 0.6
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Power (diopters): 66.67

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant