

[See all 130 Products in Family](#)

**TECHSPEC® 25mm Dia. 355nm 45°, Nd:YAG Laser Line Mirror**



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock **#47-324** **20+ In Stock**

⊖ 1 ⊕ €146.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€146,00 each
Qty 6-25	€131,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Lasers Mirror **Type:**

**Physical & Mechanical Properties**

Parallelism (arcmin):

<3

>90	<b>Clear Aperture (%)</b> :
Ground	<b>Back Surface</b> :
25.00 +0.00/-0.20	<b>Diameter (mm)</b> :
6.00 ±0.20	<b>Thickness (mm)</b> :
<b>Optical Properties</b>	
10-5	<b>Surface Quality</b> :
99.5	<b>Reflection at DWL (%)</b> :
<b>Coating Specification:</b> R <sub>abs</sub> >99.5% @ 355nm @ 45° AOI R <sub>avg</sub> >99.5% @ 351 - 358nm @ 45° AOI	
351 - 358	<b>Wavelength Range (nm)</b> :
λ/10	<b>Surface Flatness (P-V)</b> :
Dielectric	<b>Coating Type</b> :
Laser Mirror (355nm)	<b>Coating</b> :
355	<b>Design Wavelength DWL (nm)</b> :
45	<b>Angle of Incidence (°)</b> :
<a href="#">Fused Silica</a> (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>
6 J/cm <sup>2</sup> @ 355nm, 20ns, 20Hz	<b>Damage Threshold, Reference:</b> <input type="checkbox"/>

<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

## Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
  - High Laser Induced Damage Threshold Specifications
  - 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
  - [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available
- TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.
- Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

## Compatible Mounts