


TECHSPEC® 25mm Dia. Linear Polarizer Film (XP42HE-40)



Stock #71-893 **20+ In Stock**

- 1 + €33.⁵⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | €33,50 each |
| Qty 11-25 | €26,80 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Linear Polarizer **Type:**

Polarization axis can be identified as follows: **Note:**

Circular Parts - Parallel to direction of notch on polarizer
Square Parts - Parallel to mark on protective film
Rectangular Parts - Parallel to first listed dimension

Physical & Mechanical Properties

25.00 +0/-0.3 **Diameter (mm):**

0.40 +/- 0.05 **Thickness (mm):**

Polarizing Film **Construction:**

Optical Properties

30,000:1 (Nominal at 555nm) **Extinction Ratio:**

Polymer Film XP42HE-40 **Substrate:** □

Transmission (%):
Single: 42.6 (nominal @ 555nm), 41.1 (average 420-700nm)
Parallel: 36.4 (nominal @ 555nm), 34.0 (average 420-700nm)
Crossed: 0.001 (nominal @ 555nm), 0.002 (average 420-700nm)

420 - 700 **Wavelength Range (nm):**

>99.99% (nominal at 555nm) **Polarization Efficiency (%):**

Environmental & Durability Factors

-10 to +60 **Operating Temperature (°C):**

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)

PRODUCT DETAILS

- Superior 30,000:1 Extinction Ratio
- Excellent Transmission from 420-700nm
- Available in a Range of Sizes
- Custom Sizes Available

TECHSPEC® Ultra-High Contrast Polarizing Film (XP42HE) are designed to produce a 30,000:1 contrast ratio from 420 – 700nm with an excellent transmission of 42.6%. These polarizing films are available in rectangular geometries in a range of sizes. TECHSPEC Ultra-High Contrast Polarizing Film (XP42HE) are easily cut to required geometries using common cutting tools for system integration. Additionally, the 500 x 1000mm version [#24-286](#) and [#71-907](#) are available with an adhesive backing to facilitate incorporation into various applications. These polarizing films are ideal for imaging, metrology, and microscopy applications where contrast sensitivity is paramount.