

[See all 9 Products in Family](#)

TECHSPEC® 25mm Dia x 25mm FL Uncoated, Si Aspheric Lens



Stock #89-358 **20+ In Stock**

[Other Coating Options](#)

1 €650.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | €650,00 each |
| Qty 6+ | €520,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

25.00 +0.00/-0.10 **Diameter (mm):**

≤10 **Centering (arcmin):**

| | |
|----------------------|----------------------------------|
| <21.8 | Centering, ETD (μm): |
| 22.5 | Clear Aperture CA (mm): |
| 2.44 | Edge Thickness ET (mm): |
| 3.80 ±0.10 | Center Thickness CT (mm): |
| Protective as needed | Bevel: |
| Diamond Turned | Edges: |
| Concave | Shape of Back Surface: |

Optical Properties

| | |
|---------------|--|
| 25.00 @4000nm | Effective Focal Length EFL (mm): |
| 0.50 | Numerical Aperture NA: |
| 22.50 | Back Focal Length BFL (mm): |
| Silicon (Si) | Substrate: □ |
| 4000 | Aspheric Design Wavelength (nm): |
| λ/6 | Asphere Figure Error, RMS @ 632.8nm: |
| Uncoated | Coating: |
| <0.3 | Surface Accuracy, P-V (μm): |
| 60-40 | Surface Quality: |
| 1.00 | f#: |
| 3.422 @5μm | Index of Refraction (n_d): |
| 43.582 | Radius R₂ (mm): |
| 1200 - 7000 | Wavelength Range (nm): |
| Infinite | Conjugate Distance: |
| 4000 | Focal Length Specification Wavelength (nm): |

Material Properties

| | |
|------|---|
| 2.55 | Coefficient of Thermal Expansion CTE (10⁻⁶/°C): |
|------|---|

Regulatory Compliance

| | |
|----------------------|------------------------------------|
| View | Certificate of Conformance: |
|----------------------|------------------------------------|

Product Details

- Diffraction-Limited Performance
- Low Density and Dispersion
- Ideal for Weight Sensitive IR Applications
- Available with BBAR (1650-3000nm) or Mid-Wave Infrared (3000-5000nm) AR Coatings

TECHSPEC® Silicon Aspheric Lenses are high performance, lightweight solutions for BBAR and Mid-Wave Infrared (MMIR) applications and are ideal alternatives for costly ZnSe lenses and brittle Germanium lenses. These lenses are available with efficient broadband AR coatings for the BBAR (1650-3000nm) or MMR (3000-5000nm) spectral regions. TECHSPEC Silicon Aspheric Lenses feature the mechanical and thermal properties required to withstand many of the effects of harsh environments including fluctuations in temperature and pressure. Because silicon is a low density material, these lenses are also ideal for weight-sensitive systems, such as those found in many defense applications.

Compatible Mounts