

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25mm Dia. X 175mm FL, NIR I Coated, Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock #18-095 3-4 DAYS

- 1 +

€145,00

ADD TO CART

Qty 1-5

€145,00

Qty 6+

€116,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00 -0.025

Effective Focal Length EFL (mm):

|                                                                                                                                                    |
|----------------------------------------------------------------------------------------------------------------------------------------------------|
| 175.00 @587.6nm                                                                                                                                    |
| <b>Back Focal Length BFL (mm):</b><br>172.94                                                                                                       |
| <b>Coating:</b><br>NIR I (600-1050nm)                                                                                                              |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.5% @ 600 - 1050nm                                                                             |
| <b>Substrate:</b> <br><a href="#">Fused Silica</a> (Corning 7980) |
| <b>Surface Quality:</b><br>40-20                                                                                                                   |
| <b>Power (P-V) @ 632.8nm:</b><br>3 Rings                                                                                                           |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>0.5 Rings                                                                                                  |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                                                           |
| <b>Centering (arcmin):</b><br><1                                                                                                                   |
| <b>Center Thickness CT (mm):</b><br>3.01 ±0.10                                                                                                     |
| <b>Edge Thickness ET (mm):</b><br>2.03                                                                                                             |
| <b>Radius R<sub>1</sub> (mm):</b><br>80.23                                                                                                         |
| <b>Clear Aperture CA (mm):</b><br>24                                                                                                               |
| <b>f/#:</b><br>7                                                                                                                                   |
| <b>Numerical Aperture NA:</b><br>0.07                                                                                                              |
| <b>Type:</b><br>Plano-Convex Lens                                                                                                                  |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                                        |
| <b>Wavelength Range (nm):</b><br>600 - 1050                                                                                                        |
| <b>Damage Threshold, Reference:</b> <br>7 J/cm² @ 1064nm, 10ns  |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |