


**TECHSPEC® 25mm Dia. x 1mm Thick, BBAR (2000-5000nm) Coated Calcium Fluoride Window**



TECHSPEC Calcium Fluoride (CaF<sub>2</sub>) Windows

Stock **#23-515** 3-4 DAYS

⊖ 1 ⊕ **€187,50**

ADD TO CART

Qty 1-10

€187,50

Qty 11+

€168,75

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Abbe Number (v<sub>d</sub>):**  
94.99

**Axis Orientation:**  
Random

**Bevel:**

|                                                                                                                                                         |
|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| Protective as needed                                                                                                                                    |
| <b>Clear Aperture (%)</b> :<br>90                                                                                                                       |
| <b>Clear Aperture CA (mm)</b> :<br>22.50                                                                                                                |
| <b>Diameter (mm)</b> :<br>25.00 +0.0/-0.1                                                                                                               |
| <b>Thickness (mm)</b> :<br>1.00 ±0.1                                                                                                                    |
| <b>Coating</b> :<br>BBAR (2000-5000nm)                                                                                                                  |
| <b>Coating Specification</b> :<br>R <sub>avg</sub> <1.5% @ 2000-5000nm<br>R <sub>abs</sub> <3.0% @ 2000-5000nm<br>R <sub>avg</sub> <1.75% @ 2000-4000nm |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C)</b> :<br>18.85                                                                             |
| <b>Density (g/cm³)</b> :<br>3.18                                                                                                                        |
| <b>Edges</b> :<br>Fine Ground                                                                                                                           |
| <b>Index of Refraction n<sub>d</sub></b> :<br>1.434                                                                                                     |
| <b>Knoop Hardness (kg/mm²)</b> :<br>158.3                                                                                                               |
| <b>Parallelism (arcmin)</b> :<br><1                                                                                                                     |
| <b>Poisson's Ratio</b> :<br>0.26                                                                                                                        |
| <b>Substrate</b> :<br>Calcium Fluoride (CaF <sub>2</sub> ) Vacuum UV Grade                                                                              |
| <b>Surface Flatness (P-V)</b> :<br>1λ                                                                                                                   |
| <b>Surface Quality</b> :<br>40-20                                                                                                                       |
| <b>Type</b> :<br>Protective Window                                                                                                                      |
| <b>Wavelength Range (nm)</b> :<br>2000 - 5000                                                                                                           |
| <b>Young's Modulus (GPa)</b> :<br>75.8                                                                                                                  |

## Regulatory Compliance

|                                                             |
|-------------------------------------------------------------|
| <b>RoHS 2015</b> :<br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance</b> :<br><a href="#">View</a> |
| <b>Reach 235</b> :<br><a href="#">Compliant</a>             |