

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25mm Dia. X 25mm FL, VIS 0<sup>+</sup> Inked, Double-Convex Lens



Stock #47-365-INK 3-5 DAYS

[Other Coating Options](#)



1



€54,50

ADD TO CART

Qty 1-9

€54,50

Qty 10+

€49,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00 ±0.025

Back Focal Length BFL (mm):

|                                                                                                   |
|---------------------------------------------------------------------------------------------------|
| 22.47                                                                                             |
| <b>Effective Focal Length EFL (mm):</b><br>25.00                                                  |
| <b>Coating:</b><br>VS 0° (425-675nm)                                                              |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm                             |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-SF5</a>                               |
| <b>Surface Quality:</b><br>40-20                                                                  |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                             |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                       |
| <b>Centering (arcmin):</b><br><1                                                                  |
| <b>Bevel:</b><br>Protective bevel as needed                                                       |
| <b>Center Thickness CT (mm):</b><br>8.00                                                          |
| <b>Center Thickness Tolerance (mm):</b><br>±0.10                                                  |
| <b>Edge Thickness ET (mm):</b><br>2.90                                                            |
| <b>Radius R<sub>1</sub>=R<sub>2</sub> (mm):</b><br>31.94                                          |
| <b>Clear Aperture CA (mm):</b><br>24.00                                                           |
| <b>f/#:</b><br>1.00                                                                               |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6                                       |
| <b>Focal Length Tolerance (%):</b><br>±1                                                          |
| <b>Numerical Aperture NA:</b><br>0.50                                                             |
| <b>Type:</b><br>Double-Convex Lens                                                                |
| <b>Wavelength Range (nm):</b><br>425 - 675                                                        |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>5 J/cm <sup>2</sup> @ 532nm, 10ns |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |