

TECHSPEC® 25mm Dia x 75mm FL 3-5µm Coated, Hybrid Ge Aspheric Lens



Stock **#68-266** CLEARANCE CONTACT US

- 1 + **€969,00**

ADD TO CART

Qty 1-5
€969,00
Qty 6+
€775,20
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
75.00 @ 4000nm

Numerical Aperture NA:
0.17

Back Focal Length BFL (mm):

72.79
Substrate: Germanium (Ge)
Aspheric Design Wavelength (nm): 4000
Asphere Figure Error, RMS @ 632.8nm: λ/6
Coating: BBAR (3000-5000nm)
Coating Specification: R _{avg} <3.0% @ 3 - 5μm
Surface Accuracy, P-V (μm): 0.3
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 24.0
Edge Thickness ET (mm): 2.39
Center Thickness CT (mm): 2.80 ±0.10
f/#: 2.94
Bevel: Protective bevel as needed
Edges: Diamond Turned
Radius R₂ (mm): 100.8
Shape of Back Surface: Concave
Type: Aspheric Lens
Wavelength Range (nm): 3000 - 5000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View