

TECHSPEC[®] 25mm Dia. x 75mm FL 785nm V-Coat, UV PCX Lens



Stock **#25-916** 5 In Stock

-

1

+

€175^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€175,00 each
Qty 6-25	€140,00 each
Qty 26-49	€131,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

25.00 +0.0/-0.025

Diameter (mm):

Protective as needed

Bevel:

4.43	Center Thickness CT (mm):
<1	Centering (arcmin):
24	Clear Aperture CA (mm):
2.08	Edge Thickness ET (mm):

Optical Properties

75.00 @ 587.6nm	Effective Focal Length EFL (mm):
Fused Silica	Substrate:
3	f#:
0.17	Numerical Aperture NA:
785nm V-Coat	Coating:
71.96	Back Focal Length BFL (mm):
R _{abs} <0.25% @ 785nm	Coating Specification:
785	Design Wavelength DWL (nm):
±1	Focal Length Tolerance (%):
34.39	Radius R ₁ (mm):
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- <0.25% Reflection at 785nm
- 5 - 50mm Diameters Available
- 10 - 250mm EFL Designs Available
- 405nm, 532nm, 1064nm, and 1550nm V-Coated Options Offered

TECHSPEC® Laser Line Coated Fused Silica PCXLenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.