

**TECHSPEC® 25mm Dia x 75mm FL NIR I Coated, Illumination Grade PCX Cylinder Lens**



Stock #69-754 **1 In Stock**

⊖ 1 ⊕ €81<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€81,00 each
Qty 6-25	€73,00 each
Qty 26-49	€70,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Cylinder Lens, Plano-Convex **Type:**

**Physical & Mechanical Properties**

25.00 **Diameter (mm):**

3.06 **Center Thickness CT (mm):**

±0.1	Center Thickness Tolerance (mm):
+0.0/-0.2	Dimensional Tolerance (mm):
1.00	Edge Thickness ET (mm):

## Optical Properties

75.00	Effective Focal Length EFL (mm):
N-BK7	Substrate: <input type="checkbox"/>
3	f#:
0.17	Numerical Aperture NA:
NIR I (600-1050nm)	Coating:
600 - 1050	Wavelength Range (nm):
72.89	Back Focal Length BFL (mm):
R <sub>avg</sub> ≤ 0.5% @ 600 - 1050nm	Coating Specification:
±3	Focal Length Tolerance (%):
38.89	Radius R <sub>1</sub> (mm):
60-40	Surface Quality:
7 J/cm <sup>2</sup> @ 1064nm, 10ns	Damage Threshold, By Design: <input type="checkbox"/>

## Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

### Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- N-BK7 Substrate for Broadband Performance
- Cost-Effective for OEM Integration
- Multiple Coating Options Available

TECHSPEC® Illumination Grade PCX Cylinder Lenses are similar to Plano-Convex (PCX) lenses in profile, but include a portion of a cylinder instead of a sphere. These lenses focus light in one dimension and can transform a point of light into a line. TECHSPEC® Illumination Grade PCX Cylinder Lenses are available in circular and rectangular versions, along with multiple coating options. Cylinder lenses are ideal for line projection in machine vision applications or guidance systems.

**Note:** For negative focal length cylinder lenses, see our [TECHSPEC® Illumination Grade PCV Cylinder Lenses](#).



## Technical Information

Circular And Rectangular Cylinder Lenses

