

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#) / [UCi Series Fixed Focal Length Lenses](#)

[See all 49 Products in Family](#)

**TECHSPEC® 25mm**



25mm UCi Series Fixed Focal Length Lens



Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit

1

€235<sup>.00</sup>

ADD TO CART

Volume Pricing

Qty 1+ €235,00 each

Need More? [Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Product Downloads

- STEP:step
- PDF Drawing:pdf
- IGES:igs
- Spec Sheets:pdf
- Zemax
- eDrawing:eprt
- EO Spec Sheet

General

<b>Product Family:</b>	UCi Series	<b>Type:</b>	Fixed Focal Length Lens
<b>IR Cut Filter:</b>	No	<b>Imaging Lens Type:</b>	High Performance Lens with Compact Form Factor and Fixed Aperture

Physical & Mechanical Properties

<b>Iris Option:</b>	Fixed	<b>Length (mm):</b>	31.50
<b>Maximum Diameter (mm):</b>	26.5	<b>Outer Diameter (mm):</b>	26.5
<b>Weight (g):</b>	38	<b>Maximum Rear Protrusion (mm):</b>	2.54

Optical Properties

<b>Horizontal Field of View @ Max Sensor Format:</b>	60.8mm - 16.4°	<b>Field of View at Max Sensor Format:</b>	Horizontal: 59.6mm - 16.4° Vertical: 44.6mm - 12.3° Diagonal: 74.8mm - 20.4°
<b>Horizontal Field of View, 1/1.8" Sensor:</b>	60.8mm - 16.4°	<b>Horizontal Field of View, 1/2" Sensor:</b>	54.0mm - 14.6°
<b>Horizontal Field of View, 1/2.5" Sensor:</b>	48.9mm - 13.2°	<b>Horizontal Field of View, 1/3" Sensor:</b>	40.4mm - 11.0°
<b>Horizontal Field of View, 1/4" Sensor:</b>	30.3mm - 8.2°	<b>Maximum Image Circle (mm):</b>	9.00
<b>Numerical Aperture NA:</b>	0.0312	<b>Number of Elements:</b>	7 (5)

Object Side:		(Groups):	
<b>Focal Length FL (mm):</b>	25.00	<b>Working Distance (mm):</b>	200 - ∞
<b>Aperture (f/#):</b>	f/1.85	Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.  <b>Select Your Country/Region:</b>	
<b>Coating Specification:</b>	λ/4 MgF <sub>2</sub>		
<b>Object Space Principal Plane (mm):</b>	29.11	<b>Image Space Principal Plane (mm):</b>	-12.34
<b>Maximum Distortion (%):</b>	-0.15	<b>Exit Pupil Position (mm):</b>	-44.48
<b>Lens Wavelength Range:</b>	VIS		
<b>Sensor</b>			
<b>Optimized Sensor Format:</b>	1/2.5"	<b>Maximum Sensor Format:</b>	1/1.8"
<b>Pixel Size (μm):</b>	1.85		
<b>Threading &amp; Mounting</b>			
<b>Filter Thread:</b>	N/A	<b>Mount:</b>	C-Mount
<b>Environmental &amp; Durability Factors</b>			
<b>Storage Temperature (°C):</b>	<b>-20 to +60</b>	<b>Type of Ruggedization:</b>	Industrial (Fixed Aperture with Simplified Mechanics)
<b>Regulatory Compliance</b>			
<b>Certificate of Conformance:</b>	<a href="#">View</a>		

## Product Details

- Up to 1/1.8", C-Mount, S-Mount Lens
- Up to 12 MegaPixels, 1.85μm Pixel Size Sensors
- Instrumentation (UCi) versions of our UC Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 4mm to 35mm Focal Length

TECHSPEC® UCi Series Fixed Focal Length Lenses utilize the same optics as the TECHSPEC UC Series Lenses and feature 4K resolution. These lenses are designed for small pixels ≤2.2μm and offer a wide range of fixed apertures for a variety of applications. While optimized for 1/2.5" sensors, many focal length options can be used on sensors up to 1/1.8". TECHSPEC® UCi Series Fixed Focal Length Lenses are ideal for OEM applications that require small, robust, and lightweight imaging solutions.

**Note:** For adjustable aperture options, see our [TECHSPEC® UC Series Fixed Focal Length Lenses](#).

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

**UC Series:** Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

**UCi Series:** Simplified mechanics featuring fixed apertures with compact housing. **Industrial Ruggedization** for reduced size, cost, and locked focus.

**UCr Series:** All optics glued in place and a locking C-clamp focus ring. **Stabilized Ruggedization** for reduced pixel shift and improved focus stability.

**UCw Series:** Waterproof, designed to meet IEC **Ingress Protection** Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.

## Technical Information

## Accessories

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**

Note: Compatible accessories for in

r products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
<a href="#">MORE+</a>	C-Mount to M12 Adapter for UCi Lens		#12-879	€48,00 <a href="#">Request Quote</a>	20+ In Stock <input type="text" value="1"/>

## Related Products



#33-305 - 25mm UC Series Fixed Focal Length Lens  
€260,00

Qty



#58-207 - 25mm FL f/2.5, Blue Series M12 Lens  
€81,00

Qty



#59-871 - 25mm C Series Fixed Focal Length Lens  
€260,00

Qty



USAF 1951 Glass Slide Resolution Targets

## Frequently Purchased Together



#33-305 - 25mm UC Series Fixed Focal Length Lens  
€260,00

Qty



#33-564 - 25mm Cx Series Fixed Focal Length Lens  
€245,00

Qty



#33-988 - Basler ace acA1920-40gm Monochrome GigE Camera  
€580,00

Qty










































































#34-212 - Type-A to Micro-B, USB 3.0 Locking Cable, 8m  
€92,00

















































Qty

## Compatible Cameras

	Title	Type	Compare	Stock Number	Price	Buy
<a href="#">MORE+</a>	Allied Vision Alvium 1800 U-501m NIR, 1/2.5" 5MP C-Mount, Right Angle USB 3.1 NIR Camera (Partial Housing)	NIR Camera		#19-554	€270,00 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/>
<a href="#">MORE+</a>	Allied Vision Alvium 1800 U-501m NIR, 1/2.5" 5.0MP C-Mount, USB 3.0	NIR Camera		#19-553	€270,00 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/>














































	Title	Type	Compare	Stock Number	Price	Buy
	NIR Camera (Partial Housing)					
	 Allied Vision Alvim 1800 U-501m NIR, 1/2.5" 5.0MP C-Mount, USB 3.0 NIR Camera					 <input type="text" value="1"/> 
<div style="border: 1px solid black; padding: 5px; background-color: white;"> <p>Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.</p> <p><b>Select Your Country/Region:</b></p> </div>						
	 Allied Vision Alvim 1800 U-501m NIR, 1/2.5" 5MP C-Mount, Right Angle USB 3.1 NIR Camera	NIR Camera		#19-548	€280,00 Request Quote	 <input type="text" value="1"/> 
	 Allied Vision Alvim 1800 U-500m, 1/2.5" 5.0MP C-Mount, USB 3.0 Monochrome Camera (Partial Housing)	Monochrome Camera		#14-138	€290,00 Request Quote	 <input type="text" value="1"/> 
	 Allied Vision Alvim 1800 U-500m, 1/2.5" 5.0MP C-Mount, Right Angle USB 3.1 Monochrome Camera (Partial Housing)	Monochrome Camera		#14-144	€290,00 Request Quote	 <input type="text" value="1"/> 
	 Allied Vision Alvim 1800 U-500c, 1/2.5" 5.0MP C-Mount, USB 3.0 Color Camera (Partial Housing)	Color Camera		#14-139	€300,00 Request Quote	 <input type="text" value="1"/> 
	 Allied Vision Alvim 1800 U-500c, 1/2.5" 5.0MP C-Mount, Right Angle USB 3.1 Color Camera (Partial Housing)	Color Camera		#14-145	€300,00 Request Quote	 <input type="text" value="1"/> 
	 Allied Vision Alvim 1800 U-500m, 1/2.5" 5.0MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#14-126	€300,00 Request Quote	3 In Stock <input type="text" value="1"/> 
	 Allied Vision Alvim 1800 U-500m, 1/2.5" 5.0MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#14-130	€300,00 Request Quote	 <input type="text" value="1"/> 
	 Allied Vision Alvim 1800 U-500c, 1/2.5" 5.0MP C-Mount, USB 3.0 Color Camera	Color Camera		#14-127	€310,00 Request Quote	 <input type="text" value="1"/> 
	 Allied Vision Alvim 1800 U-500c, 1/2.5" 5.0MP C-Mount, Right Angle USB 3.1 Color Camera	Color Camera		#14-131	€310,00 Request Quote	 <input type="text" value="1"/> 
	 LUCID Vision Labs Phoenix™ PHX064S-CC, Sony IMX178, 6.3MP, Color Camera	Color Camera		#13-702	€335,00 Request Quote	 <input type="text" value="1"/> 
	 LUCID Vision Labs Phoenix™ PHX064S-CC-IX, Sony IMX178,	Color Camera		#13-704	€335,00 Request Quote	 <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
	6.3MP, Color Camera					
	LUCID Vision Labs Phoenix™ PHX064S-MC, IMX178, 6.3MP Monochrome Camera					<b>CONTACT US</b> 1 
<div style="border: 1px solid black; padding: 5px; background-color: white;"> <p>Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.</p> <p><b>Select Your Country/Region:</b></p> </div>						
	LUCID Vision Labs Phoenix™ PHX064S-MC-IX, Sony IMX178, 6.3MP, Monochrome Camera	Monochrome Camera		#13-703	€335,00 <a href="#">Request Quote</a>	<b>CONTACT US</b> 1 
	LUCID Vision Labs Phoenix™ PHX023S-CC, Sony IMX392, 2.3MP, Color Camera	Color Camera		#13-662	€371,00 <a href="#">Request Quote</a>	<b>CONTACT US</b> 1 
	LUCID Vision Labs Phoenix™ PHX023S-CC-IX, Sony IMX392, 2.3MP, Color Camera	Color Camera		#13-668	€371,00 <a href="#">Request Quote</a>	<b>CONTACT US</b> 1 
	LUCID Vision Labs Phoenix™ PHX023S-MC, Sony IMX392, 2.3MP, Monochrome Camera	Monochrome Camera		#13-661	€371,00 <a href="#">Request Quote</a>	<b>CONTACT US</b> 1 
	LUCID Vision Labs Phoenix™ PHX023S-MC-IX, Sony IMX392, 2.3MP, Monochrome Camera	Monochrome Camera		#13-667	€371,00 <a href="#">Request Quote</a>	<b>CONTACT US</b> 1 
	LUCID Vision Labs Phoenix™ PHX032S-CC, Sony IMX265, 3.2 MP, Color Camera (Recertified 05-P)	Color Camera		#11-465-RCD-05P <span style="background-color: green; color: white; padding: 2px;">RECERTIFIED</span>	€375,20 <a href="#">Request Quote</a>	<b>1 In Stock</b> 1 
	Basler ace2 a2A3840-45umBAS Monochrome USB3 Basic Camera	Monochrome Camera		#16-621	€379,00 <a href="#">Request Quote</a>	<b>CONTACT US</b> 1 
	Basler ace2 a2A3840-13gmBAS Monochrome GigE Basic Camera	Monochrome Camera		#16-597	€379,00 <a href="#">Request Quote</a>	<b>1 In Stock</b> 1 
	Allied Vision Alvium 1800 U-240m, 1/2.3" 2.35MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#17-085	€380,00 <a href="#">Request Quote</a>	<b>CONTACT US</b> 1 
	Allied Vision Alvium 1800 U-240c, 1/2.3" 2.35MP C-Mount, USB 3.0 Color Camera	Color Camera		#17-086	€390,00 <a href="#">Request Quote</a>	<b>1 In Stock</b> 1 
	LUCID Vision Labs Triton™ TRI064S-CC, Sony IMX178, 6.3MP, Color Camera	Color Camera		#13-718	€402,00 <a href="#">Request Quote</a>	<b>1 In Stock</b> 1 

	Title	Type	Compare	Stock Number	Price	Buy
	 Basler ace2 a2A3840-45uc Color USB3 Bas Camera				€402,00	<b>CONTACT US</b> 1 
	 Basler ace2 a2A3840-13gc Color GigE Bas Camera					<b>CONTACT US</b> 1 
	 LUCID Vision Labs Triton™ TRI064S- MC, Sony IMX178, 6.3MP, Monochrome Camera	Monochrome Camera		#13-717	€402,00 Request Quote	1 In Stock 1 
	 Basler ace2 a2A1920- 160umBAS Monochrome USB3 Basic Camera	Monochrome Camera		#16-617	€402,00 Request Quote	3 In Stock 1 
	 Basler ace2 a2A1920-51gmBAS Monochrome GigE Basic Camera	Monochrome Camera		#16-593	€402,00 Request Quote	3 In Stock 1 
	 BFS-U3-63S4C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#11-510	€414,00 Request Quote	2 In Stock 1 
	 BFS-PGE-63S4C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#12-756	€414,00 Request Quote	3 In Stock 1 
	 BFS-U3-63S4M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#11-509	€414,00 Request Quote	1 In Stock 1 
	 BFS-PGE-63S4M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#12-755	€414,00 Request Quote	<b>CONTACT US</b> 1 
	 Basler Ace acA3088-57um USB 3.0 Monochrome Camera	Monochrome Camera		#37-213	€419,00 Request Quote	2 In Stock 1 
	 Basler ace acA3088-16gm Monochrome GigE Camera	Monochrome Camera		#37-205	€419,00 Request Quote	1 In Stock 1 
	 BFS-U3-23S3C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#12-748	€421,00 Request Quote	<b>CONTACT US</b> 1 
	 BFS-PGE-23S3C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#12-754	€421,00 Request Quote	4 In Stock 1 
	 BFS-U3-23S3M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#12-747	€421,00 Request Quote	<b>CONTACT US</b> 1 
	 BFS-PGE-23S3M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#12-753	€421,00 Request Quote	1 In Stock 1 
	 LUCID Vision Labs Triton™ TRI023S- CC, Sony IMX392, 2.3MP, Color Camera	Color Camera		#13-714	€422,00 Request Quote	3 In Stock 1 











































Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**

	Title	Type	Compare	Stock Number	Price	Buy
	 LUCID Vision Labs Triton™ TRI0200 MC, Sony IMX265, 2.3MP, Monochrome Camera					<b>CONTACT US</b> <input type="text" value="1"/> 
	 Basler ace2 a2A1920-51gc Color GigE Basic Camera	Color Camera		#16-594	Request Quote	<b>CONTACT US</b> <input type="text" value="1"/> 
	 Allied Vision Alvium G1-240m, 1/2.3" 2.4MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-543	€430,00 Request Quote	<b>CONTACT US</b> <input type="text" value="1"/> 
	 Basler ace2 a2A1920-160ucBAS Color USB3 Basic Camera	Color Camera		#16-618	€435,00 Request Quote	<b>CONTACT US</b> <input type="text" value="1"/> 
	 Basler Ace acA3088-57uc USB 3.0 Color Camera	Color Camera		#37-214	€439,00 Request Quote	<b>CONTACT US</b> <input type="text" value="1"/> 
	 Basler ace acA3088-16gc Color GigE Camera	Color Camera		#37-206	€439,00 Request Quote	3 In Stock <input type="text" value="1"/> 
	 Allied Vision Alvium G1-240c, 1/2.3" 2.4MP C-Mount, GigE PoE Color Camera	Color Camera		#23-544	€440,00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Alvium G1-500m, 1/2.5" 5MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-551	€460,00 Request Quote	2 In Stock <input type="text" value="1"/> 
	 LUCID Vision Labs Phoenix™ PHX032S-CC, Sony IMX265, 3.2 MP, Color Camera	Color Camera		#11-465	€469,00 Request Quote	4 In Stock <input type="text" value="1"/> 
	 LUCID Vision Labs Phoenix™ PHX032S-CC-IX, Sony IMX265, 3.2 MP, Color Camera	Color Camera		#13-678	€469,00 Request Quote	<b>CONTACT US</b> <input type="text" value="1"/> 
	 LUCID Vision Labs Phoenix™ PHX032S-MC, Sony IMX265, 3.2 MP, Monochrome Camera	Monochrome Camera		#11-464	€469,00 Request Quote	2 In Stock <input type="text" value="1"/> 
	 LUCID Vision Labs Phoenix™ PHX032S-MC-IX, Sony IMX265, 3.2 MP, Monochrome Camera	Monochrome Camera		#13-677	€469,00 Request Quote	<b>CONTACT US</b> <input type="text" value="1"/> 
	 Allied Vision Alvium G1-500c, 1/2.5" 5MP C-Mount, GigE PoE Color Camera	Color Camera		#23-552	€480,00 Request Quote	2 In Stock <input type="text" value="1"/> 
	 Basler ace2 a2A3840-45umPRO Monochrome USB3 Pro Camera	Monochrome Camera		#16-633	€505,00 Request Quote	<b>CONTACT US</b> <input type="text" value="1"/> 
	 Basler ace2 a2A3840-13gmPRO Monochrome GigE Pro Camera	Monochrome Camera		#16-609	€505,00 Request Quote	<b>CONTACT US</b> <input type="text" value="1"/> 

































Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**

	Title	Type	Compare	Stock Number	Price	Buy
	 LUCID Vision Labs Triton™ TRI03000-CC, Sony IMX335, 3.2MP, Color Camera					4 In Stock <input type="text" value="1"/> 
	 LUCID Vision Labs Triton™ TRI03000-MC, Sony IMX335, 3.2MP, Monochrome Camera	Camera		#13-715	Request Quote	CONTACT US <input type="text" value="1"/> 
	 Allied Vision Alvium 1800 U-319m, 1/1.8" 3.2MP C-Mount, USB 3.0 Monochrome Camera (Partial Housing)	Monochrome Camera		#14-875	€520,00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace2 a2A3840-45ucPRO Color USB3 Pro Camera	Color Camera		#16-634	€525,00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace2 a2A3840-13gcPRO Color GigE Pro Camera	Color Camera		#16-610	€525,00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Allied Vision Alvium 1800 U-319c, 1/1.8" 3.2MP C-Mount, USB 3.0 Color Camera (Partial Housing)	Color Camera		#14-876	€530,00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 IDS U3-3880CP-C-HQ, USB 3.0, 1/1.8" Color Camera	Color Camera		#16-544	€530,00 Request Quote	15 In Stock <input type="text" value="1"/> 
	 Allied Vision Alvium 1800 U-319m, 1/1.8" 3.2MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#14-871	€530,00 Request Quote	20+ In Stock <input type="text" value="1"/> 
	 Allied Vision Alvium 1800 U-319m, 1/1.8" 3.2MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#14-873	€530,00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 IDS U3-3880CP-M-GL, USB 3.0, 1/1.8" Monochrome Camera	Monochrome Camera		#16-545	€530,00 Request Quote	5 In Stock <input type="text" value="1"/> 
	 Basler ace2 a2A1920-160umPRO Monochrome USB3 Pro Camera	Monochrome Camera		#16-629	€535,00 Request Quote	3 In Stock <input type="text" value="1"/> 
	 Basler ace2 a2A1920-51gmPRO Monochrome GigE Pro Camera	Monochrome Camera		#16-605	€535,00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Basler ace acA2500-14um Monochrome USB 3.0 Camera (Recertified 05-P)	Monochrome Camera		#88-325-RCD-05P RECERTIFIED	€536,00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Alvium 1800 U-319c, 1/1.8" 3.2MP C-Mount, USB 3.0 Color Camera	Color Camera		#14-872	€540,00 Request Quote	3 In Stock <input type="text" value="1"/> 





























Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

	Title	Type	Compare	Stock Number	Price	Buy
	Allied Vision Alvium 1800 U-319c, 1/1.8" 3.2MP C-Mount, Right Angle, USB 3.1 Color Camera					<b>CONTACT US</b> 1 
	Basler ace acA2500-14gm Monochrome GigE Camera	Camera		#85-165	Request Quote	1 In Stock 1 
	LUCID Vision Labs Triton™ TRI051S-CC, Sony IMX547, 5MP, Color Camera	Color Camera		#18-483	€545,00 Request Quote	<b>CONTACT US</b> 1 
	LUCID Vision Labs Triton™ TRI051S-MC, Sony IMX547, 5MP, Monochrome Camera	Monochrome Camera		#18-484	€545,00 Request Quote	3 In Stock 1 
	Basler ace2 a2A1920-51gcPRO Color GigE Pro Camera	Color Camera		#16-606	€560,00 Request Quote	<b>CONTACT US</b> 1 
	BFS-PGE-31S4C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#11-528	€565,00 Request Quote	2 In Stock 1 
	BFS-U3-31S4C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#12-750	€565,00 Request Quote	<b>CONTACT US</b> 1 
	BFS-PGE-31S4M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#11-527	€565,00 Request Quote	1 In Stock 1 
	BFS-U3-31S4M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#12-749	€565,00 Request Quote	1 In Stock 1 
	Basler ace acA2500-14gc Color GigE Camera	Color Camera		#85-166	€570,00 Request Quote	1 In Stock 1 
	Basler ace2 a2A1920-160ucPRO Color USB3 Pro Camera	Color Camera		#16-630	€570,00 Request Quote	<b>CONTACT US</b> 1 
	Basler ace acA2040-35gm Monochrome GigE Camera	Monochrome Camera		#35-915	€570,00 Request Quote	<b>CONTACT US</b> 1 
	Allied Vision Alvium G1-319m, 1/1.8" 3.2MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-547	€580,00 Request Quote	1 In Stock 1 
	BFLY-PGE-31S4M/C-C 1/1.8" Blackfly® PoE GigE Color Camera	Color Camera		#34-510	€585,00 Request Quote	1 In Stock 1 
	BFLY-PGE-31S4M/C-C 1/1.8" Blackfly® PoE GigE Monochrome Camera	Monochrome Camera		#34-511	€585,00 Request Quote	3 In Stock 1 
	Allied Vision Alvium G1-319c, 1/1.8" 3.2MP C-Mount, GigE PoE Color Camera	Color Camera		#23-548	€590,00 Request Quote	5 In Stock 1 

















































Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.































**Select Your Country/Region:**

	Title	Type	Compare	Stock Number	Price	Buy
<a href="#">MORE+</a>	 Basler ace acA2040-35gc Color GigE Camera				€600,00	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 M2020, 1/1.8" Monochrome, DALSA Genie Nano GigE PoE Camera					2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 C2020-IR, 1/1.8" Color, DALSA Genie Nano GigE PoE Camera	Color Camera		#34-961	€620,00 Request Quote	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Basler ace acA3800-10gc Color GigE Camera	Color Camera		#89-979	€620,00 Request Quote	CONTACT US <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Allied Vision Mako G-319 1/1.8" Color CMOS Camera (Recertified 05-P)	Color Camera		#36-175-RCD-05P RECERTIFIED	€636,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 BFS-PGE-50S4C-C, PoE GigE Blackfly® S, Color Camera (Recertified 05-P)	Color Camera		#22-080-RCD-05P RECERTIFIED	€650,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 IDS U3-3270CP-C-HQ REV.2.2, USB 3.0, 1/1.8" Color Camera	Color Camera		#16-528	€670,00 Request Quote	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Basler ace acA2500-14um Monochrome USB 3.0 Camera	Monochrome Camera		#88-325	€670,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Allied Vision Alvium 1800 U-511m, 1/1.8" 5.1MP C-Mount, Right Angle USB 3.1 Monochrome Camera (Partial Housing)	Monochrome Camera		#19-566	€670,00 Request Quote	CONTACT US <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Allied Vision Alvium 1800 U-511m, 1/1.8" 5.1MP C-Mount, USB 3.0 Monochrome Camera (Partial Housing)	Monochrome Camera		#19-565	€670,00 Request Quote	CONTACT US <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Allied Vision Alvium 1800 U-511c, 1/1.8" 5.1MP C-Mount, Right Angle USB 3.1 Color Camera (Partial Housing)	Color Camera		#19-578	€680,00 Request Quote	CONTACT US <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Allied Vision Alvium 1800 U-511c, 1/1.8" 5.1MP C-Mount, USB 3.0 Color Camera (Partial Housing)	Color Camera		#19-577	€680,00 Request Quote	CONTACT US <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Allied Vision Alvium 1800 U-511m, 1/1.8" 5.1MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#19-560	€680,00 Request Quote	3 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Allied Vision Alvium 1800 U-511m, 1/1.8" 5.1MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#19-559	€680,00 Request Quote	CONTACT US <input type="text" value="1"/> 

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.































**Select Your Country/Region:**

	Title	Type	Compare	Stock Number	Price	Buy
	 Allied Vision Alvium 1800 U-511c, 1/1.8" 5.1MP C-Mount, Right Angle, USB 3.1 Color Camera					1 In Stock <input type="text" value="1"/> 
<div style="border: 1px solid black; padding: 5px; background-color: white;"> <p>Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.</p> <p><b>Select Your Country/Region:</b></p> </div>						
	 Allied Vision A 1800 U-511c, 1/1.8" 5.1MP C-Mount, USB 3.0 Color Camera	Color Camera		#19-571	Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace acA2040-55um Monochrome USB 3.0 Camera	Monochrome Camera		#35-921	€700,00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace acA2500-14uc Color USB 3.0 Camera	Color Camera		#88-326	€705,00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Basler ace acA3800-14uc Color USB 3.0 Camera	Color Camera		#89-992	€720,00 Request Quote	2 In Stock <input type="text" value="1"/> 
	 Basler ace acA2040-55uc Color USB 3.0 Camera	Color Camera		#35-922	€720,00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 BFS-PGE-50S4C-C, PoE GigE Blackfly® S, Color Camera	Color Camera		#22-080	€740,00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 BFS-U3-50S4C-C, USB 3.1 Blackfly® S, Color Camera	Color Camera		#22-765	€740,00 Request Quote	2 In Stock <input type="text" value="1"/> 
	 BFS-PGE-50S4M-C, PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#22-081	€740,00 Request Quote	2 In Stock <input type="text" value="1"/> 
	 BFS-U3-50S4M-C, USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#22-766	€740,00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Allied Vision Alvium G5-500m, 1/2.5" 5MP C-Mount, 5GigE PoE Monochrome Camera	Monochrome Camera		#23-619	€750,00 Request Quote	6 In Stock <input type="text" value="1"/> 
	 Allied Vision Alvium G5-500c, 1/2.5" 5MP C-Mount, 5GigE PoE Color Camera	Color Camera		#23-620	€760,00 Request Quote	1 In Stock <input type="text" value="1"/> 
	 IDS U3-3890SE-C-HQ, USB 3.0, 1/1.7" Color Camera	Color Camera		#24-138	€765,00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 IDS U3-3890SE-M-GL, USB 3.0, 1/1.7" Monochrome Camera	Monochrome Camera		#24-139	€765,00 Request Quote	4 In Stock <input type="text" value="1"/> 
	 Allied Vision Mako G-319 1/1.8" Monochrome CMOS Camera	Monochrome Camera		#36-174	€840,00 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Allied Vision Mako G-319 1/1.8" Color CMOS Camera	Color Camera		#36-175	€860,00 Request Quote	CONTACT US <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
<a href="#">MORE+</a>	 Allied Vision Manta G-0319 1/1.8\" data-bbox="198 45 278 78"/> Color Camera				€868,95	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 BFS-U3-32S4C USB 3.1 Blackfly S, Color Camera					1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 BFS-U3-32S4M-C USB 3.1 Blackfly S, Monochrome Camera	Monochrome Camera		#36-453	€905,00 Request Quote	3 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Pixelink PL-D7715CU-BL, 1/2.3\" data-bbox="198 205 310 238"/> 15MP, Board Level USB 3.0 Color Camera	Color Camera		#89-400 <b>CLEARANCE</b>	€928,95 Request Quote	<b>CONTACT US</b> <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Basler ace acA2040-120um Monochrome USB 3.0 Camera	Monochrome Camera		#35-923	€980,00 Request Quote	3 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Pixelink USB 3.0 Autofocus Monochrome Camera	Monochrome Camera		#34-787	€995,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Basler ace acA2040-120uc Color USB 3.0 Camera	Color Camera		#35-924	€1.000,00 Request Quote	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Allied Vision Manta G-0319 1/1.8\" data-bbox="198 445 278 478"/> Monochrome Camera	Monochrome Camera		#34-716	€1.010,00 Request Quote	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 IDS U3-3070CP-C-HQ, USB 3.0, 1/1.8\" data-bbox="198 505 278 538"/> Color Camera	Color Camera		#16-512	€1.020,00 Request Quote	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 IDS U3-3070CP-M-GL, USB 3.0, 1/1.8\" data-bbox="198 555 278 588"/> Monochrome Camera	Monochrome Camera		#16-513	€1.020,00 Request Quote	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Pixelink USB 3.0 Autofocus Monochrome Camera (Recertified 05-P)	Monochrome Camera		#34-787-RCD-05P <b>RECERTIFIED</b>	€1.060,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Allied Vision Manta G-319C Color CMOS PoE Camera	Color Camera		#37-511	€1.070,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Allied Vision Manta G-319B Monochrome CMOS PoE Camera	Monochrome Camera		#37-510	€1.070,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 GS3-U3-32S4C-C 1/1.8\" data-bbox="198 785 300 818"/> FLIR Grasshopper®3 High Performance USB 3.0 Color Camera	Color Camera		#33-535	€1.155,00 Request Quote	3 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 GS3-U3-32S4M-C 1/1.8\" data-bbox="198 835 300 868"/> FLIR Grasshopper®3 High Performance USB 3.0 Monochrome Camera	Monochrome Camera		#33-534	€1.155,00 Request Quote	1 In Stock <input type="text" value="1"/> 

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**

	Title	Type	Compare	Stock Number	Price	Buy
<a href="#">MORE+</a>	 Allied Vision Manta G-319C Color CMOS PoE Camera (Recertified 05)				€1.160,00	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Pixelink PL-D775CU-T, 1/2.3" 5.0MP, C-Mount USB 3.0 Color Camera				Quote	3 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Pixelink PL-D7718CU-BL, 1/2.3", 18MP, C-Mount USB 3.0 Color Board Level Camera	Color Camera		#21-071	€1.185,00 Request Quote	CONTACT US <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Pixelink PL-D775MU-T, 1/2.5" 5.0MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#89-386	€1.185,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Pixelink PL-D7718CU-T, 1/2.3", 18MP, C-Mount USB 3.0 Color Camera	Color Camera		#21-070	€1.295,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Pixelink M-Series M18C-CYL Microscopy Color Camera	Color Microscopy Camera		#21-072	€1.510,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 M2050, 1/1.8" Monochrome, Teledyne DALSA Genie Nano 5GigE PoE Camera	Monochrome Camera		#16-024	€1.600,00 Request Quote	4 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 C2050-IR, 1/1.8" Color, Teledyne DALSA Genie Nano 5GigE PoE Camera	Color Camera		#16-025	€1.615,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Oryx® ORX-10GS-32S4C-C Color 10GigE	Color Camera		#19-797	€1.775,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Oryx® ORX-10GS-32S4M-C Mono 10GigE	Monochrome Camera		#19-796	€1.775,00 Request Quote	CONTACT US <input type="text" value="1"/> 
<a href="#">MORE+</a>	 LUCID Vision Labs Atlas10 ATX051S-CC, Sony IMX537, 5.0MP, Color Camera	Color Camera		#18-477	€1.905,00 Request Quote	CONTACT US <input type="text" value="1"/> 
<a href="#">MORE+</a>	 LUCID Vision Labs Atlas10 ATX051S-MC, Sony IMX537, 5.0MP, Monochrome Camera	Monochrome Camera		#18-478	€1.905,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 PL-D7718CU-AFE Pixelink USB 3.0 Autofocus Color Camera	Color Camera		#21-078	€2.085,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Lumenera INFINITY5 5-3 Microscopy Color Camera	Color Microscopy Camera		#16-678	€3.725,00 Request Quote	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a>	 Lumenera INFINITY5 5-3 Microscopy Monochrome Camera	Monochrome Microscopy Camera		#16-677	€3.725,00 Request Quote	1 In Stock <input type="text" value="1"/> 

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

# Resources

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**

## Media Type

- Application Note
- Video
- Published Article
- FAQ
- Glossary
- Technical Tool



[View More](#)