

TECHSPEC® 25mm Dia. x 85mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-359** ☐ In Stock
[Other Coating Options](#)

1 **€118,00**

ADD TO CART

Qty 1-5
€118,00
Qty 6+
€94,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

85.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 81.21
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 24.00
Centering (arcmin): <1
Center Thickness CT (mm): 8.01 ±0.20
Center Thickness CT 1 (mm): 5.01 ±0.10
Center Thickness CT 2 (mm): 3.00 ±0.10
Radius R₁ (mm): 55.68
Radius R₂ (mm): -38.37
Radius R₃ (mm): -146.45
Edge Thickness ET (mm): 6.05
Substrate:  N-SK11 / N-SF5
Surface Quality: 40-20
f/#: 3.4
Numerical Aperture NA: 0.15
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View