


265µm with 16 Fiber, Optical Grade Plastic Light Guide



Stock #02-537 3-4 DAYS

- 1 + **€2,80**

ADD TO CART

Qty 1+

€2,80

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Acceptance Angle (°):
61.00

Minimum Bend Radius (mm):
55.00

Substrate: ☐
Acrylic

Attenuation (dB/m):
0.70

Numerical Aperture NA:
0.51

Number of Fibers: 16.00
Operating Temperature (°C): -55 to +70
Outer Diameter (mm): 2.2
Core Diameter (µm): 255.00
Fiber Diameter (µm): 265.00
Length (ft): Cut to Order, Minimum 10
Construction: Black Polyethylene Jacket
Index of Refraction n_d - Core: 1.492
Index of Refraction n_d - Cladding: 1.402
Attenuation (dB/km): 150 - 300 (@ 650nm)
Numerical Aperture (NA) Tolerance: ±0.03
Diameter Tolerance (%): ±6

Regulatory Compliance

RoHS 2015: Compliant
Reach 197: Compliant
Certificate of Conformance: View