

[See all 32 Products in Family](#)

## 266nm, 8-12mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal- $\pi$ Shaper\_266\_Q-10

See More by [AdlOptica](#)



#25-844: 266nm, 8-12mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal- $\pi$ Shaper\_266\_Q-10



Stock **#25-844** **1 In Stock**

⊖ 1 ⊕ €3.040<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	€3.040,00 each
Qty 5+	€2.710,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Focal- $\pi$ Shaper\_266\_Q-10 **Model Number:**

Beam Shaper **Type:**

#12-322

Compatible Adapter:

## Physical & Mechanical Properties

29.00	Length (mm):
50	Weight (g):
20	Clear Aperture CA (mm):
42.00	Diameter (mm):
8 - 12	Input Beam Diameter, $1/e^2$ (mm):

## Optical Properties

>99	Transmission (%):
266	Design Wavelength DWL (nm):
250 - 275	Wavelength Range (nm):
TEM <sub>00</sub>	Input Beam Mode:
<1.5	Typical Input Beam Mode Quality, M <sup>2</sup> :
±20	Input Beam Divergence (mrad):

## Electrical

0.2	Maximum Input Power, CW (kW):
-----	-------------------------------

## Threading & Mounting

M30 x0.75	Inner Thread:
M30 x0.75	Outer Thread:

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 250:

## Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica piShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal- $\pi$ Shaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal- $\pi$ Shapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

## Technical Information



