


TECHSPEC® 25mm Diameter x 35mm EFL Aspherized Achromatic Lens



Aspherized Achromatic Lenses



Stock **#49-663** ☐ In Stock

1 **€157,00**

ADD TO CART

Qty 1-5

€157,00

Qty 6+

€125,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.05

Effective Focal Length EFL (mm):
35.00

Back Focal Length BFL (mm): 28.14
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 22.00
Centering (arcmin): ≤5
Center Thickness CT (mm): 11.58
Center Thickness CT 1 (mm): 9.00
Center Thickness CT 2 (mm): 2.58
Radius R₁ (mm): 23.50
Radius R₂ (mm): −36.70
Radius R₃ (mm): 323.01
Edge Thickness ET (mm): 7.90
Substrate: N-LAK8 / N-SF57
Surface Quality: 60-40, glass surfaces only
f#: 1.4
Numerical Aperture NA: 0.36
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Note: VIS 0° Coating on First Surface, Second Surface is Aspheric Polymer
Operating Temperature (°C): -20°C to 80°C
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View