

TECHSPEC® 25mm, f/1.8 Cw Series Fixed Focal Length Lens



25mm Focal Length



Stock **#15-647** 3-4 DAYS



1



€310,00

ADD TO CART

Qty 1+

€310,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Fixed

Length (mm):
41.40

Horizontal Field of View, 1/2" Sensor:
12.1°

Horizontal Field of View, 2/3" Sensor:

16.6°
Filter Thread: M30.5 x0.50 (Female)
Maximum Diameter (mm): 37.77
Outer Diameter (mm): 34.1
Horizontal Field of View, 1/3" Sensor: 9.1°
Maximum Rear Protrusion (mm): 4.2
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.0533
Horizontal Field of View @ Max Sensor Format: 38.3mm - 16.6°
Number of Elements (Groups): 7 (6)
Note: C-Mount compatible with O-ring 25mm ID x2mm
Horizontal Field of View, 1/1.8" Sensor: 13.6°
Horizontal Field of View, 1/2.5" Sensor: 11.0°
Type: Fixed Focal Length Lens
Diameter (mm): 38.00
Focal Length FL (mm): 25.00
Primary Magnification PMAG: 0.232
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/1.8
Coating: 425 - 675nm BBAR
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 21.65
Horizontal Field of View, 1/4" Sensor: 6.8°
Object Space Principal Plane (mm): 24.53
Image Space Principal Plane (mm): -12.44
Field of View at Max Sensor Format: Horizontal: 19.8° Vertical: 14.9° Diagonal: 24.6°
Maximum Distortion (%): 0.22
Exit Pupil Position (mm): -15.69
Environmental Rating: IPX7 and IPX9K
Lens Wavelength Range: VIS
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

