

[See all 20 Products in Family](#)

3-Pin Lemo® Connector



Stock #90-652 **NEW** 1 In Stock

- 1 + €30⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€30,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Note:
Power connector for #59-178, #59-179 and #90-625 to #90-630 and #90-634 to #90-643

Regulatory Compliance

Compliant

RoHS 2015:

[View](#)

Certificate of Conformance:

Product Details

- Ultra-Wide Adjustable Transimpedance Gain from 10^2 to 10^{11} V/W
- Exceptional Low-Noise, High-Sensitivity Single-Beam Detection
- Optimized for Absolute Optical Power Measurements
- Designed for Direct, Alignment-Free Integration

Variable Gain Photoreceivers feature an ultra-wide adjustable transimpedance gain from 10^2 to 10^{11} V/W, enabling precise measurement of optical signals across a broad power range. Engineered for ultra-low noise performance, these photoreceivers achieve noise equivalent power (NEP) as low as $6\text{ fW}/\sqrt{\text{Hz}}$, ensuring accurate detection of extremely weak optical signals. Designed for single-beam detection, they provide maximum sensitivity and dynamic range, allowing for simple, alignment-free integration into optical systems. Variable Gain Photoreceivers are ideal for applications such as photonics research, optical communication testing, and precision low-light measurements.

Note: Power supply sold separately. Please see specifications for more details.
