

[See all 11 Products in Family](#)

**TECHSPEC® 25mm LT Series Fixed Focal Length Lens**



25mm FL Front, #14-363



Stock **#14-363** CLEARANCE **1 In Stock**

⊖ 1 ⊕ €1.765<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€1.765,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Diameter includes liquid lens **Note:**

Fixed Focal Length Lens **Type:**

**Integrated Liquid Lens Model:**  
Optutune EL-10-30-TC-VIS-5D

**Imaging Lens Type:**  
Integrated Liquid Lens to Adjust Focus Electronically

## Physical & Mechanical Properties

**Iris Option:**  
Fixed

**Length (mm):**  
99.51

**Maximum Diameter (mm):**  
78.5

**Outer Diameter (mm):**  
78.5

**Weight (g):**  
366.5

**Maximum Rear Protrusion (mm):**  
0

## Optical Properties

**Horizontal Field of View @ Max Sensor Format:**  
165.5mm - 49.1°

**Field of View at Max Sensor Format:**  
Horizontal: 127.1mm - 32.3°  
Vertical: 94mm - 24.3°  
Diagonal: 162.2mm - 40.3°

**Horizontal Field of View, 1.1" Sensor:**  
127.1mm - 32.3°

**Horizontal Field of View, 1" Sensor:**  
114.9mm - 29.4°

**Horizontal Field of View, 2/3" Sensor:**  
77.9mm - 32.3°

**Horizontal Field of View, 1/1.8" Sensor:**  
63.5mm - 16.6°

**Horizontal Field of View, 1/2" Sensor:**  
56.4mm - 14.8°

**Horizontal Field of View, 1/2.5" Sensor:**  
51.0mm - 13.4°

**Horizontal Field of View, 1/3" Sensor:**  
42.2mm - 11.1°

**Horizontal Field of View, 1/4" Sensor:**  
31.5mm - 8.3°

**Maximum Image Circle (mm):**  
17.60

**Numerical Aperture NA, Object Side:**  
0.02

**Number of Elements (Groups):**  
9 (6)

**Focal Length FL (mm):**  
25.00

**Working Distance (mm):**  
150 - ∞

**Aperture (f/#):**  
f/2.8

**Coating:**  
M4 MgF<sub>2</sub>

**Coating Specification:**  
M4 MgF<sub>2</sub>

**Entrance Pupil Position (mm):**  
52.38

**Object Space Principal Plane (mm):**  
72.02

**Image Space Principal Plane (mm):**  
4.02

**Maximum Distortion (%):**  
-2.93

**Exit Pupil Position (mm):**  
-107.78

**Lens Wavelength Range:**  
VIS

## Sensor

**Maximum Sensor Format:**  
1.1"

## Threading & Mounting

**Filter Thread:**

M62 x 0.75 (Female)

Mount:

C-Mount

## Environmental & Durability Factors

Storage Temperature (°C):

-20 to +60

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- 1.1" Sensor, C-Mount Lens, up to 12 MegaPixels, 3.45µm Pixel Size Sensor
- Integrated Liquid Lens Allows for Dynamic Autofocus
- Liquid Tunable (LT) Lens Maximizes the Liquid Lens Capabilities for Resolution, Range and Focus Speed
- 12 to 25mm Focal Length


TECHSPEC® LT Series Fixed Focal Length Lenses feature a high-resolution f/2.8 optical design with an integrated Optotune liquid lens for fast electronic focus. The increased light throughput f/2.8 aperture is ideal for high-speed machine vision applications. When combined with an appropriate camera and software, the focus tunable liquid lens provides the active focus control needed to achieve an autofocus solution. These C-Mount lenses are optimized for 1.1" sensors and have front filter threading to integrate imaging filters to meet application requirements. TECHSPEC® LT Series Fixed Focal Length Lenses are ideal for machine vision and factory automation applications where focusing at multiple distances is required, such as quality inspection systems, rapid automation, and package sorting. The TECHSPEC® LT Series Fixed Focal Length Lenses won the [Gold-Level 2021 Vision Systems Design Innovators Award](#) and [third place 2021 reader's choice inspect Award](#).




inspect  
award 2021  
winner

**Note:** Hirose cables (2 length options) and Lens Driver are required for operation and sold separately.


## Technical Information




#14-363, 25mm LT Series Fixed Focal Length Lens, Distortion Plot




#14-363, 25mm LT Series Fixed Focal Length Lens, Relative Illumination Plot




#14-363, 25mm LT Series Fixed Focal Length Lens, Working Distance versus Field of View Plot



#14-363, 25mm LT Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 300mm Working Distance, f2.8




#14-363, 25mm LT Series Fixed Focal Length Lens, Depth of Field Plot, 300mm Working Distance, f2.8



#14-363, 25mm LT Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 750mm Working Distance, f2.8



#14-363, 25mm LT Series Fixed Focal Length Lens, Depth of Field Plot, 750mm Working Distance, f2.8



**Compatible Cameras**