

# 3.0 OD 50mm Sq, Absorptive ND Filter

See More by [Hoya](#)



Stock **#48-098** 3-4 DAYS

- 1 + **€95,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| €95,00                        |
| Qty 11+                       |
| €84,00                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):  
50.0 x 50.0

Optical Density OD (Average):

|                                                               |
|---------------------------------------------------------------|
| 3.0 ±0.3                                                      |
| <b>Glass/Filter Number:</b><br><a href="#">Hoya ND-0.3</a>    |
| <b>Substrate:</b> <input type="checkbox"/><br>ND Filter Glass |
| <b>Length (mm):</b><br>50.00                                  |
| <b>Coating:</b><br>Uncoated                                   |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.51          |
| <b>Surface Quality:</b><br>80-50                              |
| <b>Transformation Temperature (°C):</b><br>490                |
| <b>Thickness (mm):</b><br>3.00                                |
| <b>Thickness Tolerance (mm):</b><br>±0.5                      |
| <b>Transmission (%):</b><br>0.1 (average)                     |
| <b>Type:</b><br>Neutral Density Filter                        |
| <b>Width (mm):</b><br>50.00                                   |
| <b>Blocking Wavelength Range (nm):</b><br>400 - 700           |
| <b>Dimensional Tolerance (mm):</b><br>±0.2                    |
| <b>Parallelism (mm):</b><br><0.02                             |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |