

300mm Cobra Max RGB-IR Line Light



300mm Cobra MaxLine Light



Stock **#73-952** 1 In Stock

-

1

+

€8.500⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€8.500,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Type of Illumination:	
LED	
Note:	
Lights are fan cooled. See datasheet for additional mounting, spectral, and irradiance information	
Manufacturer:	
ProPhotonix	

Line Light	Geometry:
Illumination Mode: Ethernet Controlled, Continuous, Strobed	
Physical & Mechanical Properties	
300.00	Length (mm):
300.00 x 173.50	Dimensions (mm):
Collimated (M2)	Lens Position:
Optical Properties	
RGB-IR	Color:
455, 532.5, 630, 855	Wavelength:
10-112	Working Distance (mm):
Electrical	
120000	Maximum Trigger Frequency (Hz):
Hardware & Interface Connectivity	
Straight	Connector:
24	Operating Voltage (V):
Power Supply: Power supply required and sold separately. USA: #73-977	
2m braided power cable included	Length of Cable (m):
Threading & Mounting	
Aluminum T-Slot Extrusion	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Intensities up to 3140kLux
- 100, 300, or 600mm Length Options Available
- White, Red, Multispectral, and SWIR Illumination Options Available

ProPhotonix COBRA™ MAX LED Line Lights are slim, compact LED line lights available in lengths of 100, 300, or 600mm in red, white, multispectral, or SWIR illumination options. These line lights feature Chip-on-Board LED technology which offers greater uniformity, thermal performance, and intensity while maintaining a compact size compared to traditional surface mount LED constructions. ProPhotonix COBRA™ MAX LED Line Lights multispectral option offers RGB-IR illumination and the ability to control each wavelength independently. The available easy-to-use comprehensive software package can be customized to meet specific application needs and is downloadable from a QR code included with the units. These lights are ideal for many linescan inspection applications such as solar cell inspection, semiconductor inspection, food sorting, and flat panel display inspection.

Note: Required 24V Power Supply, [#73-977](#), sold separately. Optional Lens Kits are available to adjust the working distance by changing the position of the projection lens.