

266nm Flat Top Beam Shaper | πShaper 12_12_266_HP

See More by [AdlOptica](#)



Stock **#15-498** [CONTACT US](#)

- 1 + **€9.584,00**

ADD TO CART

Qty 1-4
€9.584,00

Qty 5+
€8.626,00

Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):

266

Diameter (mm):

42.00

Entrance Beam Diameter, 1/e² (mm):

12.0 - 12.1

Model Number: πShaper 12_12_266_HP
Length (mm): 358.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <530
Wavelength Range (nm): 250 - 270
Style: Flat Top
Damage Threshold, By Design: ☐ 3 J/cm² @ 5ns (typical)
Output Diameter, FWHM (mm): 10.6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant