


TECHSPEC® 2X, Protected Aluminum Canopus® Reflective Beam Expander



TECHSPEC® Canopus™ Reflective Beam Expanders



Stock **#37-193** [CONTACT US](#)

- 1 + **€567,00**

ADD TO CART

Qty 1-5
€567,00
Qty 6+
€500,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Coating:

Protected Aluminum (400-12000nm)
Design Wavelength DWL (nm): Broadband
Entrance Aperture (mm): 4
Exit Aperture (mm): 8
Expansion Power: 2X
Substrate: ☐ Aluminum 6061-T6
Height (mm): 25.4
Length (mm): 71.00
Surface Quality: 40-20
Type: Beam Expander
Weight (g): 133
Width (mm): 38.10
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >70% @ 700 - 2000nm R _{avg} >97% @ 2 - 12μm
Wavelength Range (nm): 400 - 12000
Style: Fixed Magnification
Surface Roughness (Angstroms): <50 RMS
Wavefront Error, P-V: ≤ λ/10 on-axis for a 1mm Dia. Input Beam

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View