

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Broadband Dielectric Coated Right Angle Mirrors](#)

[See all 30 Products in Family](#)

TECHSPEC®

30.0mm 750 - 1100nm Coated)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit



Broadband Dielectric Coated Right Angle Mirrors

Stock #87-402 **5 In Stock**

1

€281^{,00}

ADD TO CART

Volume Pricing	
Qty 1-5	€281,00 each
Qty 6-25	€225,00 each
Qty 26-49	€211,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

- STEP:step
- Curve:pdf
- PDF Drawing:pdf
- IGES:igs
- eDrawing:eprt
- EO Spec Sheet
- [Download All](#)

General

Type: Right Angle Mirror

Physical & Mechanical Properties

Clear Aperture (%): 90

Dimensional Tolerance (mm): ±0.1

Length of Hypotenuse (mm): 42.40

Length of Legs (mm): 30.00

Optical Properties

Coating Type: Dielectric

Coating: Dielectric Mirror (750-1100nm)

Wavelength Range (nm): 750 - 1100

Substrate: [N-BK7](#)

Angle Tolerance (arcmin): ±2

Coating Specification:
Hypotenuse:
R_{avg} >98% @ 750 - 1100nm (0 - 45°)
R_{avg} >99% @ 750 - 1100nm (0°)

Surface Quality: 40-20

Damage Threshold, By Design: 1 J/cm² @ 1064nm, 20ns, 20Hz

Power (fringes) @ 632.8nm: 1.25

Irregularity (fringes) @ 632.8nm: 0.50

Regulatory Compliance

RoHS 2015: **Compliant**

Reach 209: **Compliant**

Certificate of Conformance: [View](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Need different specs or measurements?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Greater Than 98% Reflection Over Broad Wavelength Ranges
- High Reflectivity for all Polarization States
- Reflect Light at 90°
- **Standard Metal Coated Right Angle Mirrors** Also Available


TECHSPEC® Broadband Dielectric Coated Right Angle Mirrors (Hypotenuse Coated) are designed for beam steering or precision alignment applications utilizing multiple laser sources or operating from the visible to near-infrared spectra. These mirrors feature improved reflection compared to standard metal coated mirrors, increasing system performance by decreasing energy loss. These right angle mirrors are easily mounted and integrated into optical systems. TECHSPEC® Broadband Dielectric Coated Right Angle Mirrors (Hypotenuse Coated) reflect light at 90° and have greater than 98% reflection over broad wavelength ranges. These mirrors feature a N-BK7 substrate and are available in a variety of leg lengths.

Note: These right angle mirrors are not recommended for use in applications where light is reflected off the coated hypotenuse from inside the prism.


Technical Information

Image above shows light reflecting off the coated hypotenuse.


Related Products




Broadband Dielectric $\lambda/10$ Mirrors



Right Angle Prism Mirrors (Hypotenuse Coated)



Right Angle Prisms




Prism and Beamsplitter Mounts

Frequently Purchased Together



#33-946 - 25mm Dia, 0.25 Numerical Aperture, NIR Coated, Aspheric Lens
 €349,00

Qty



No #33-946 - 25mm Dia, 0.25 Numerical Aperture, NIR Coated, Aspheric Lens
 €451,00

Qty



Aspheric Lens
 €599,00

Qty



#87-405 - 50.0mm 750 - 1100nm, N-BK7 Right Angle Mirrors (Hypotenuse Coated)
 €394,00

Qty

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Resources

Media Type

- Application Note
- Video
- FAQ
- Glossary

CASE STUDIES

Laser Optics for Eye Surgery

TRENDING IN OPTICS

Increasing Challenges for Sourcing Laser Optics...

CASE STUDIES

Using IR Spectroscopy for Counterfeit Drug Detection

APPLICATION NOTE

Metallic Mirror Coatings

VIDEO

Optical Mirrors Review

FAQ

What is the difference between a first-surface...

[View More](#)