

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 30mm Dia. X 300mm FL, VIS-NIR, Inked, Achromatic Lens



Stock #49-378-INK [CONTACT US](#)

[Other Coating Options](#)



1



€154,00

ADD TO CART

Qty 1-5

€154,00

Qty 6+

€123,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Effective Focal Length EFL (mm):

300.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 296.85
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 29.00
Centering (arcmin): <1
Center Thickness CT (mm): 7.00 ±0.20
Center Thickness CT 1 (mm): 4.50 ±0.10
Center Thickness CT 2 (mm): 2.50 ±0.10
Radius R ₁ (mm): 184.40
Radius R ₂ (mm): -133.95
Radius R ₃ (mm): -394.96
Edge Thickness ET (mm): 6.12
Substrate:  N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 10.00
Numerical Aperture NA: 0.05
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View