

30µm Aperture Diameter, Chrome on Glass Aperture



Stock **#90-736** NEW **3 In Stock**

-

1

+

€185^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€185,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

Physical & Mechanical Properties	
25.4	Outer Diameter (mm):
30 ±3.0	Fixed Aperture Diameter (µm):
0.06 ±0.004	Thickness (inches):
±0.1	Thickness Tolerance (mm):
	Thickness (mm):

1.52

Optical Properties

Low Reflective ChromeCoating:

Regulatory Compliance

ViewCertificate of Conformance:

Product Details

- Chrome Coating on Glass Substrate
- Ideal for Precise Beam Control, Modulation, or Optical Alignment
- Pinhole Diameters Ranging from 10µm to 1,000µm

Chrome Coated Glass Optical Apertures are composed of soda lime float glass with low reflective chrome coating for high-contrast performance. These apertures are designed with pinhole diameters ranging from 10µm to 1000µm. The apertures have an overall diameter of 25.4mm (1") and a thickness of 1.52mm, ensuring easy integration with a wide variety of optical mounts. Chrome coating on glass provides a stable and circular aperture diameter immune to bending or creasing. Chrome Coated Glass Optical Apertures are designed to provide high-precision light control, ideal for beam shaping, spatial filtering, and alignment in advanced photonic systems.