

TECHSPEC®

30mm Dia., 0.66 Numerical Aperture, 600-1050nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#16-984-INK** [CONTACT US](#)

[Other Coating Options](#)



1



€430,00

ADD TO CART

Qty 1-5

€430,00

Qty 6+

€344,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
30.00 ±0.025

Effective Focal Length EFL (mm):

22.50 @ 587.6nm
Numerical Aperture NA: 0.66
Back Focal Length BFL (mm): 13.53
Substrate: NSF5
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: NIR+ (600-1050nm)
Coating Specification: R _{avg} <0.5% @ 600 - 1050nm @ ±30° AOI R _{abs} <1.5% @ 600 - 1050nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 27.00
Edge Thickness ET (mm): 6.62
Center Thickness CT (mm): 15.00 ±0.10
f#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View