

TECHSPEC® 30mm Dia. x 75mm FL, MgF₂ Coated, Inked, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#32-498-INK** [CONTACT US](#)

[Other Coating Options](#)

- 1 +

€135,00

ADD TO CART

Qty 1-5

€135,00

Qty 6+

€108,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Effective Focal Length EFL (mm): 75.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 67.44
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 29.00
Centering (arcmin): <1
Center Thickness CT (mm): 11.40 ±0.20
Center Thickness CT 1 (mm): 8.40 ±0.10
Center Thickness CT 2 (mm): 3.00 ±0.10
Radius R₁ (mm): 40.51
Radius R₂ (mm): -38.68
Radius R₃ (mm): -922.04
Edge Thickness ET (mm): 8.40
Substrate: ☐ N-SSK3 / N-SF10
Surface Quality: 40-20
f/#: 2.5
Numerical Aperture NA: 0.20
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View