

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 31.75mm Sq., 2.5X, Protected Gold Off-Axis Ellipsoidal Mirror



Protected Gold Off-Axis Ellipsoidal Mirror

Stock #12-498 3-4 DAYS



1



€335,00

ADD TO CART

Qty 1-5
€335,00

Qty 6+
€301,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Magnification:
2.5X

Substrate:
Aluminum 6061-T6

Surface Quality:
60-40

Surface Roughness (Angstroms): <100 RMS
Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Dimensions (mm): 31.75 x31.75
Off-Set Angle (°): 65.44
Type: Off-Axis Ellipsoidal Mirror
Wavelength Range (nm): 700 - 10000
Y Offset (mm): 49.38
Image Distance (mm): 83.82
Object Distance (mm): 33.02

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View