

## 34.9mm Dia. x 21.6mm FL, Aspheric Condenser Lens



Stock **#19-520** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€47,00**

ADD TO CART

|          |
|----------|
| Qty 1-10 |
| €47,00   |

|         |
|---------|
| Qty 11+ |
| €42,00  |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

### Get Product Downloads

**Diameter (mm):**  
34.90 +0.0/-0.2

**Effective Focal Length EFL (mm):**  
21.60

**Numerical Aperture NA:**  
0.81

|                                                   |
|---------------------------------------------------|
| Back Focal Length BFL (mm):<br>11                 |
| Substrate: <div><div></div><div>H-K51</div></div> |
| Focal Length Tolerance (%):<br>±5                 |
| Coating:<br>Uncoated                              |
| Centering (arcmin):<br>≤30                        |
| Surface Quality:<br>80-50 (typical)               |
| Clear Aperture CA (mm):<br>31.41                  |
| Edge Thickness ET (mm):<br>2.91                   |
| Center Thickness CT (mm):<br>19.00 ±0.30          |
| f/#:<br>0.62                                      |
| Bevel:<br>Protective bevel as needed              |
| Diameter of Asphere (mm):<br>34.9                 |
| Radius R <sub>2</sub> (mm):<br>71.12              |
| Shape of Back Surface:<br>Convex                  |
| Type:<br>Condenser Lens                           |
| Wavelength Range (nm):<br>350 - 2000              |
| Conjugate Distance:<br>Infinite                   |

## Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS:<br><a href="#">Compliant</a>                  |
| Certificate of Conformance:<br><a href="#">View</a> |