

TECHSPEC®

35.0mm Dia. x 50.0mm FL, VIS-NIR, Inked, Plano-Convex Lens



Stock **#38-552-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

€66,00

ADD TO CART

Qty 1-9
€66,00

Qty 10+
€59,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
35.00 ±0.025

Effective Focal Length EFL (mm):

50.00 @ 587.6nm
Back Focal Length BFL (mm): 44.40
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 8.50 ±0.10
Edge Thickness ET (mm): 1.67
Radius R₁ (mm): 25.84
Clear Aperture CA (mm): 34
f/#: 1.43
Numerical Aperture NA: 0.35
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View