

[See all 298 Products in Family](#)

TECHSPEC® 350nm CWL, 50mm Dia., Hard Coated OD 4.0 10nm Bandpass Filter



TECHSPEC Hard Coated OD 4.0 10nm Bandpass Filters

Stock **#39-185** **3 In Stock**

[Additional Bandwidths](#)

⊖ 1 ⊕ €710⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | €710,00 each |
| Qty 6-25 | €568,00 each |
| Qty 26-49 | €532,50 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Bandpass Filter **Type:**

General Filtering **Typical Applications:**

Physical & Mechanical Properties

| | |
|---|---|
| 50.00 +0.0/-0.1 | Diameter (mm): |
| 45 | Clear Aperture CA (mm): |
| Mounted in Black Anodized Ring | Construction: |
| Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2 | Physical Durability: |
| 3.5 ±0.5 typical | Substrate Thickness (mm): |
| Optical Properties | |
| 0 | Angle of Incidence (°): |
| ≥4.0 | Optical Density OD (Average): |
| 350.00 ±2.0 | Center Wavelength CWL (nm): |
| 10.00 ±2.0 | Full Width-Half Max FWHM (nm): |
| ±2.0 | Full Width-Half Max FWHM Tolerance (nm): |
| Fused Silica (Corning 7980) | Substrate: <input type="checkbox"/> |
| >85 | Minimum Transmission (%): |
| Hard Coated | Coating: |
| 80-50 | Surface Quality: |
| 200 - 1200 | Blocking Wavelength Range (nm): |

Threading & Mounting

| | |
|----------|------------------------------|
| 5.0 ±0.1 | Mount Thickness (mm): |
|----------|------------------------------|

Environmental & Durability Factors

| | |
|---|----------------------------------|
| Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7 | Environmental Durability: |
|---|----------------------------------|

Regulatory Compliance

| | |
|------------------|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 247: |

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Ideal for Life Sciences or Chemical Analysis
- Available in UV, VIS, and IR Center Wavelengths
- Feature High Performance Hard Coatings
- Hard Coated OD 4.0 [5nm](#), [25nm](#), and [50nm](#) Bandpass Filters Also Available

TECHSPEC® Hard Coated OD 4.0 10nm Bandpass Filters are narrowband filters used extensively in applications including flame photometry, elemental or laser line separation, fluorescence, laser diode cleanup, or chemical detection or analysis. These optical filters offer steep slopes with deep blocking to achieve high performance in demanding applications. TECHSPEC Hard Coated OD 4.0 10nm Bandpass Filters feature durable hard coatings to minimize filter degradation while increasing transmission. The bandpass filters are available in UV, VIS, and IR center wavelengths.

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm² @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

Technical Information



All mounted TECHSPEC® Optical Filters have an arrow on the side of the mount that points to the filter-coated surface for quick reference. Filter oriented such that arrow points to filter coated surface S1. Anti-reflective (AR) coating is applied to S2.



Compatible Mounts
