

TECHSPEC® 30mm Dia. x 60mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#47-714-INK** 3-5 DAYS
[Other Coating Options](#)

- 1 + **€146,00**

ADD TO CART

Qty 1-5
€146,00
Qty 6+
€116,75
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Effective Focal Length EFL (mm):

60.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 52.50
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 29.00
Centering (arcmin): <1
Center Thickness CT (mm): 11.46 ±0.20
Center Thickness CT 1 (mm): 8.47 ±0.10
Center Thickness CT 2 (mm): 2.99 ±0.10
Radius R ₁ (mm): 32.60
Radius R ₂ (mm): -31.81
Radius R ₃ (mm): -799.64
Edge Thickness ET (mm): 7.66
Substrate:  N-SSK8 / N-SF10
Surface Quality: 40-20
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View