

TECHSPEC®

30mm Dia. x 75mm FL YAG-BBAR Coated, Double-Convex Lens



YAG-BBAR Coated Double-Convex (DCX) Lenses



Stock **#89-279** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

€58,00

ADD TO CART

Qty 1-9
€58,00

Qty 10+
€52,25

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.025

Back Focal Length BFL (mm): 73.35
Effective Focal Length EFL (mm): 75.00
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.96
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.00
Radius R₁=R₂ (mm): 76.67
Clear Aperture CA (mm): 29.00
f/#: 2.5
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.20
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 2200
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant