

[See all 65 Products in Family](#)

TECHSPEC® 3.5mm f/2.0 Sealed Cw Series Fixed Focal Length Lens



3.5mm Focal Length



Stock #15-607 **20+ In Stock**

⊖ 1 ⊕ €493⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | €493,00 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Cw Series **Product Family:**

C-Mount compatible with O-ring 25mm ID x2mm **Note:**

Fixed Focal Length Lens **Type:**

Physical & Mechanical Properties

| | |
|-------|--------------------------------------|
| Fixed | Iris Option: |
| 41.96 | Length (mm): |
| 65.00 | Maximum Diameter (mm): |
| 65 | Outer Diameter (mm): |
| 2.7 | Maximum Rear Protrusion (mm): |

Optical Properties

| | |
|--|---|
| Field of View at Max Sensor Format: Horizontal: 102.34° Vertical: 82.28° Diagonal: 116.98° | |
| 102.34° | Horizontal Field of View, 1/1.8" Sensor: |
| 94.13° | Horizontal Field of View, 1/2" Sensor: |
| 86.75° | Horizontal Field of View, 1/2.5" Sensor: |
| 74.44° | Horizontal Field of View, 1/3" Sensor: |
| 9.00 | Maximum Image Circle (mm): |
| 0.073 | Numerical Aperture NA, Object Side: |
| 10 (9) | Number of Elements (Groups): |
| 3.50 | Focal Length FL (mm): |
| 75 - ∞ | Working Distance (mm): |
| f/2 | Aperture (f/#): |
| 425 - 675nm BBAR | Coating Specification: |
| 34.70 | Entrance Pupil Position (mm): |
| -22.37 | Object Space Principal Plane (mm): |
| 32.70 | Image Space Principal Plane (mm): |
| 21.12 | Maximum Distortion (%): |
| -15.89 | Exit Pupil Position (mm): |
| VIS | Lens Wavelength Range: |

Sensor

| | |
|--------|-------------------------------|
| 1/1.8" | Maximum Sensor Format: |
| 2.74 | Pixel Size (µm): |

Threading & Mounting

| | |
|---------------------|-----------------------|
| M62 x 0.75 (Female) | Filter Thread: |
| C-Mount | Mount: |

Environmental & Durability Factors

| | |
|-------------------|-------------------------------|
| IPX7 | Environmental Rating: |
| Waterproof (IPX7) | Type of Ruggedization: |

Regulatory Compliance

| | |
|----------------------|------------------------------------|
| View | Certificate of Conformance: |
|----------------------|------------------------------------|

Product Details


- Up to 2/3", C-Mount Lens
- Waterproof (Cw) Versions of C Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- Designed to Eliminate the Need for a Protective Lens Cover

TECHSPEC® Cw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® C Series Fixed Focal Length Lenses](#). Designed to meet IEC Ingress Protection Codes IPX7 and IPX9K, these lenses withstand exposure to water up to 1 meter depth for 30 minutes and operate in close-range high pressure, high temperature water spray downs with the exception of all 3.5 and 4.5mm options which are IPX7. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface. To prevent moisture from entering the housing, the lenses are sealed with multiple O-rings. TECHSPEC® Cw Series Fixed Focal Length Lenses are designed for up to 7.5 MegaPixel, 2/3" sensors and are ideal for applications including food, pharma, automotive, and security. These lenses won the Bronze-Level 2021 Vision Systems Design Innovators Award.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a [VIS-NIR Broadband Anti-Reflection \(BBAR\) Coating](#).
- **Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- **Cr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.
- **Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- **Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- **Cw Series:** Waterproof, designed to meet IEC [Ingress Protection Code](#) IPX7 and IPX9K.


Technical Information




#15-607, 3.5mm f/2.0 Sealed Cw Series Fixed Focal Length Lens, Distortion Plot




#15-607, 3.5mm f/2.0 Sealed Cw Series Fixed Focal Length Lens, Relative Illumination Plot




#15-607, 3.5mm f/2.0 Sealed Cw Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#15-607, 3.5mm f/2.0 Sealed Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 75mm Working Distance, f2



#15-607, 3.5mm f/2.0 Sealed Cw Series Fixed Focal Length Lens, Depth of Field Plot, 75mm Working Distance, f2



#15-607, 3.5mm f/2.0 Sealed Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 150mm Working Distance, f2



#15-607, 3.5mm f/2.0 Sealed Cw Series Fixed Focal Length Lens, Depth of Field Plot, 150mm Working Distance, f2