


Siemens Star Target Array, 101 x 101mm, 59 Stars, 36 Sectors Chrome on Glass



Stock #58-835 **4 In Stock**

- 1 + €726^{,-15}

ADD TO CART

Volume Pricing

Qty 1-4	€726,15 each
Qty 5+	€690,10 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

NIST Certification:

No

Physical & Mechanical Properties

4.50	Individual Star Diameter (mm):
36.00	Number of Sectors:
59.00	Number of Stars:
90.00 x 90.00	Pattern Size (mm):
101 x 101 ±0.1	Dimensions (mm):
2.00 ±0.05	Thickness (mm):

Optical Properties

High Reflective Chrome	Coating:
1.27 - 38.5	Frequency (lp/mm):
Float Glass	Substrate:

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 223:
View	Certificate of Conformance:

PRODUCT DETAILS

- Detect Aberrations at Various Field Points

Our star target arrays are designed to identify focus errors and astigmatism along field points in the image of a vision system. With star targets located at the center, corner, and along the diagonals of the sensor, determining precision location and amplitude of the problem areas couldn't be easier. The small array features unresolved centers of 0.1mm, whereas the large array features unresolved centers of 0.15mm.