

[See all 12 Products in Family](#)

365nm, Ethernet High Intensity Coaxial Spot Light (Recertified 05-P)

See More by [Advanced Illumination](#)



Advanced Illumination Ethernet Controlled High Intensity LED Spot Lights

Stock **#21-356-RCD-05P** RECERTIFIED **1 In Stock**

-

1

+

€530^{,00}

ADD TO CART

Volume Pricing	
Qty 1+	€530,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
	Model Number:
SL162-365C1	
	LED Lifetime (hours):
50,000	
	Number of LEDs:
1	

LED Illuminator	Type of Illumination:
Note: Required Controller #18-645 ; Required Power Supply #66-855	
Advanced Illumination	Manufacturer:
Geometry:	
Spot Light	
Illumination Mode:	
Constant, Pulsed, Gated	

Physical & Mechanical Properties

85.1	Weight (g):
------	-------------

Optical Properties

UV	Color:
365	Wavelength (nm):

Hardware & Interface Connectivity

C1	Connector:
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
2	Length of Cable (m):

Environmental & Durability Factors

0 to +60	Operating Temperature (°C):
----------	-----------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Controllable via Ethernet GUI or Web Browser
- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
- Efficient Thermal Management for Long LED Life
- Compatible with [TECHSPEC® Telecentric Backlight Illuminators](#) and [Lenses](#)

Advanced Illumination Ethernet Controlled High Intensity In-Line Lights utilize a C1 connector to connect to the DCS-100E Single Output Controller (#18-645). The DCS-100E Single Output Controller allows these high intensity in-line lights to be ethernet controlled through a downloadable software package or through a Web Based Graphical User Interface (GUI). With efficient thermal management, these in-line lights are able to provide 33,000 Lux at a working distance of 100mm with a spot size of 61mm in either a continuous, pulsed, or gated operating mode. Advanced Illumination Ethernet Controlled High Intensity In-Line Lights can be overdriven in short pulses without damaging the LED through Advanced Illumination's SignaTech™ Control System which is available with the DCS-100E Controller. These lights are available in UV, Blue, Green, Red Orange, IR, or White and are compatible with the 8mm port found on many in-line illumination imaging lenses, making them an excellent choice for use with TECHSPEC® Telecentric Backlight Illuminators and telecentric lenses with an [inline illumination port](#). For applications that do not require ethernet controlled functionality, [Advanced Illumination High Intensity In-Line Lights](#) are also available.

Note: 24V power supply ([#66-855](#)) and DCS-100E Single Output Controller ([#18-645](#)) are required for use.