


34mm² Suppressed NIR DUV Photodiode w/Metal Housing



DUVPhotodiodes

Stock **#84-599** **6 In Stock**

-

1

+

€129⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€129,00 each
Qty 5-9	€114,00 each
Qty 10-24	€101,50 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

2 @0 V, 1 kΩ

Rise Time (µs):

Physical & Mechanical Properties

5.8 x5.8

Size of Active Area (mm):

Active Area (mm²):

34.0	
Optical Properties	
720.00	Peak Response Wavelength (nm):
Electrical	
0.36	Responsivity @ 980nm (AW):
Minimum: 0.5 Typical: 5	Shunt Resistance @ V=-10mV (GΩ):
0.34	Responsivity @ 633nm (AW):
0.12	Responsivity @ 200nm (AW):
800.00	Capacitance @ V _R =0V (pF):
1.6 x 10 ⁻¹⁴	Noise Equivalent Power NEP (W/ Hz ^{1/2}): @ 0 V, 200nm
5.00	Maximum Reverse Voltage (V):
Hardware & Interface Connectivity	
TO-8	Connector:
Environmental & Durability Factors	
-20 to +60	Operating Temperature (°C):
-55 to +80	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Excellent UV Sensitivity
- High Shunt Resistance
- Low Capacitance

DUV Photodiodes are ideal for a wide variety of applications, including UV spectrophotometry and analytical and medical instrumentation. DUV Photodiodes are designed for enhanced responsivity from 200 – 400nm, and with sensitivity extending down to 190nm. DUV Photodiodes feature quartz windows and either metal or ceramic housing. Models with suppressed NIR performance are also available.