

**TECHSPEC® 38.1 x 25.4mm 532nm 45°, Nd:YAG Laser Line Mirror**



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock #39-644 **4 In Stock**

⊖ 1 ⊕ €172.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€172,00 each
Qty 6-25	€153,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Laser Mirror **Type:**

**Physical & Mechanical Properties**

<3 **Parallelism (arcmin):**

85 **Clear Aperture (%):**

Commercial Polish	<b>Back Surface:</b>
38.1 x 25.4 +0.00/-0.10	<b>Dimensions (mm):</b>
6.35 ±0.20	<b>Thickness (mm):</b>
<b>Optical Properties</b>	
10-5	<b>Surface Quality:</b>
99.8	<b>Reflection at DWL (%):</b>
R <sub>abs</sub> >99.8% @ 532nm R <sub>avg</sub> >99.5% @ 523 - 537nm	<b>Coating Specification:</b>
523 - 537	<b>Wavelength Range (nm):</b>
λ/10	<b>Surface Flatness (P-V):</b>
Dielectric	<b>Coating Type:</b>
Laser Mirror (523-537nm)	<b>Coating:</b>
532	<b>Design Wavelength DWL (nm):</b>
45	<b>Angle of Incidence (°):</b>
<a href="#">Fused Silica</a> (Coming 7980)	<b>Substrate:</b> <input type="checkbox"/>
15 J/cm <sup>2</sup> @ 532nm, 20ns, 20Hz	<b>Damage Threshold, Reference:</b> <input type="checkbox"/>

<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">Compliant</a>	<b>REACH 201:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
  - High Laser Induced Damage Threshold Specifications
  - 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
  - [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available
- TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.
- Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

## Compatible Mounts